

6

5

4

3

2

1

MATERIAL AND FINISH

Insulator: Polycarbonate, UL-94V-0 rated
Contacts: Brass, Tin Plated

ELECTRICAL SPECIFICATIONS:

Current rating: 10 A 

Current rating: 15 A 

Voltage rating: 250 VAC 

Insulation resistance: 100 Mohm min. at 500 VDC

Dielectric withstanding voltage: 2000 VAC for one minute






RoHS
COMPLIANT

ORDERING CODE:

43R09-3 3 2- 1 2

- 1) COLOR
1 = BLACK
2 = GRAY

- 2) PANEL THICKNESS



RECOMMENDED
PCB LAYOUT

P/N	A	MAX. PANEL THICKNESS
42R09-3X32-150	1.5	1.5
43R09-3X32-200	2.0	2.0
43R09-3X32-250	2.5	2.5

ADDITIONAL PANEL THICKNESS
AVAILABLE ON REQUEST

TOLERANCE
UNLESS OTHERWISE SPECIFIED
X ± 1
X.X ± 0.4
X.XX ± 0.20

Power Dynamics, Inc.

Phone: 973 560-0019 Whippary, New Jersey Fax: 973 560-0076

PART: 10A/15A IEC 60320 APPL. OUTLET; STRAIGHT
PC TERMINALS; SNAP-IN, PANEL MOUNT

DRAWN BY GQ DATE: 10/09/01
CHECK BY TD DATE: 10/11/01
APPR BY PB DATE: 10/11/01

PART #: 43R09-3X32-XXX

SHEET
1 of 1

SIZE: A
SCALE: NTS
ALL DIMENSIONS FOR REFERENCE ONLY
DIMENSIONS ARE IN MILLIMETERS

REV:

REVISIONS

REV DATE CHANGE CHNG CHECK APPR

6

5

4

3

2

1