



*PARTS AVAILABLE BY SPECIAL ORDER ONLY

TO PRESS-FIT IN A $.312 \pm .003$
(7.92 ± 0.08) DIA. HOLE, IN A
.25 (6.4) MIN. THICK PANEL



M4 THREAD




*BHEHCB


*MSEHCB

BASE STYLE

TO SNAP-LOCK IN A
.187 $\pm$.003 (4.75 ± 0.08) DIA.
HOLE IN A .031-.078
(0.79-1.98) PANEL
THICKNESS




.25 (6.4)
[.20 (5.2) -5 ONLY]




FOR #6 (M3.5),
SELF TAPPING SCREW.

HEAD STYLE




STANDARD NOSE
STANDARD CLIP
"C"=.29 (7.5)

-8
STANDARD NOSE
SHORT CLIP
"C"=.24 (6.1)



-6
SHORT NOSE
SHORT CLIP
"C"=.24 (6.1)

-7
SHORT NOSE
STANDARD CLIP
"C"=.29 (7.5)



-9
NO NOSE
SHORT CLIP
"C"=.24 (6.1)

-10
NO NOSE
STANDARD CLIP
"C"=.29 (7.5)

EHCBS-A-01
EHCBS-A-19

*EHCBS-8-A-01
*EHCBS-8-A-19

*EHCBS-6-A-01
*EHCBS-6-A-19

*EHCBS-7-A-01
*EHCBS-7-A-19

*EHCBS-9-A-01
*EHCBS-9-A-19

*EHCBS-10-A-01
*EHCBS-10-A-19

*TEHCBS-A-01
*TEHCBS-A-19

*TEHCBS-8-A-01
*TEHCBS-8-A-19

*TEHCBS-6-A-01
*TEHCBS-6-A-19


*TEHCBS-7-A-01
*TEHCBS-7-A-19

*TEHCBS-9-A-01
*TEHCBS-9-A-19

*TEHCBS-10-A-01
*TEHCBS-10-A-19

SELECT BASE STYLE FROM LEFT TABLE COLUMN AND HEAD STYLE FROM THE TOP OF THE TABLE. WHERE THE COLUMN & ROWS INTERSECT IS THE CORRESPONDING PART NO.

TO FIT A $.156 \pm .003$
(4.00 ± 0.08) DIA. HOLE, IN A
.062 (1.57) THICK PC BOARD




TO SNAP-LOCK IN A $.187 \pm .003$
(4.75 ± 0.08) DIA. HOLE IN A
.031-.078 (0.79-1.98) PANEL THICKNESS

EXAMPLE:

EHCBS-7-6-01
EHCBS-7-6-19
PART NO. HEAD STYLE DIM. "A" MATERIAL

FOR DIMENSION "A" SEE CHART.




NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01),
FLAME RETARDANT: NYLON (RMS-19),
2. COLOR: NATURAL.

**ONLY TEHCBS-4-01 OR "-19" AVAILABLE IN 1/4 (6.4) SIZE

DIM. "A"	SIZE
-4**	1/4 (6.4)
-5	5/16 (7.9)
-6	3/8 (9.5)
-8	1/2 (12.7)
-10	5/8 (15.9)
-12	3/4 (19.1)
-14	7/8 (22.2)
-16	1 (25.4)

TITLE: EDGE-HOLDING CIRCUIT BOARD SUPPORTS



I	SEE CO 200035 FOR CHANGES	SK 09.26.07
H	SEE ECN #1208 FOR CHANGES	SK 11.29.06
-	SEE ENGINEERING FOR REV A-G	-
REV	DESCRIPTION	ENGR DATE

TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE # EHCBS MAT'L: SEE NOTES RE: RICHCO, INC.	DWN: S.M. DT: 12/05/01 RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060	APP: DT: PART # SEE TABLE	PRINT TYPE CA
--	--	---	------------------------------------	---------------------