

RELEASED FOR PUBLICATION 27-Nov-95

© COPYRIGHT 1996



BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

E

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
D		EB00-0466-95	9-11-95	DRT	-
E		EB00-0053-96	1-2-96	DRT	



1. TO SPLICE ANY THREE WIRES 0.5 DIA. ALUM. ALLOY. NOMINAL SOLID CONDUCTOR, OR 0.4 TO 0.9 DIA. COPPER NOMINAL SOLID CONDUCTORS.

2. FINISH CRIMPED HEIGHT 6.3 MAX.

3. THIS PART TO CONFORM TO AMP PRODUCT SPECIFICATION 108-3050 AND BT LN363 CONNECTOR WIRE INSULATED No 88, EXCEPT 342816-3.

4. SLOTS FOR TEST PROBE ACCESS. TO SUIT BT CT41A TEST PROBES.


5. 342816-3 IS THE SAME AS 342816-2, EXCEPT WITHOUT SEALANT.

PACKED AS 342816-2 BUT WITH ITALIAN LABELS	250	1-342816-3
PACKED AS 342816-2 BUT WITH SPANISH LABELS	250	1-342816-2
SEE SHT 2 SPECIAL LABELLING. RESTRICTED ISSUE FOR BT	250	1-342816-1
REELED VERSION OF TEL-SPLICE 2 3 WAY	3500	342816-4
107-3013. SEE NOTE 5	1	342816-3
107-3013	1	342816-2
SEE SHT 2 SPECIAL LABELLING. RESTRICTED ISSUE FOR BT	1	342816-1
PACKAGING SPECIFICATION	No OFF	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS IN
m.m.

TOLERANCES UNLESS
OTHERWISE SPECIFIED



THIRD ANGLE PROJECTION

LINEAR: - ± 0.5
ANGULAR: - $\pm 1^\circ$

MATERIAL

SEE LIST

FINISH

SEE LIST

DWN 31-Jan-96
D.R. TERRY

CHK J. HUTCHINSON 31-1-96

APVD J. HUTCHINSON 31-1-96

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

AMP

AMP of Great Britain Ltd,
Slansmore,
Middlesex, HA7 4RS.

NAME

ASSY. TEL-SPLICE 2
3 WAY

SIZE

CAGE CODE

DRAWING NO

A3

00779

C=342816

SCALE 10:1

SHEET 1 OF 2

REV E

4

3

2

1

RELEASED FOR PUBLICATION 27-May-95

© COPYRIGHT 1996



BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

E

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-
-	-	-	-	-	-

BODY
C342818-1

1. TO SPLICE ANY THREE WIRES 0.5 DIA. ALUM. ALLOY.
NOMINAL SOLID CONDUCTOR, OR 0.4 TO 0.9 DIA.
COPPER NOMINAL SOLID CONDUCTORS.

2. FINISH CRIMPED HEIGHT 6.3 MAX.


3 THIS PART TO CONFORM TO AMP PRODUCT SPECIFICATION
108-3050 AND BT LN363 CONNECTOR WIRE INSULATED No 88

4 SLOTS FOR TEST PROBE ACCESS. TO SUIT BT CT41A TEST PROBES.

RESTRICTED
FOR BRITISH TELECOM ONLY

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS IN
m.m



THIRD ANGLE PROJECTION

MATERIAL
SEE LIST

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

LINEAR: - ± 0.5 ANGULAR: - $\pm 1^\circ$

FINISH
SEE LIST

DWN 31-Jan-96

D.R. TERRY

CHK J. HUTCHINSON 31-1-96

APVD J. HUTCHINSON 31-1-96

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

AMP

AMP of Great Britain Ltd,
Stanmore,
Middlesex, HA7 4RS.

NAME

ASSY. TEL-SPLICE 2
3 WAY

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-342816

SCALE 10:1

SHEET 2 OF 2

REV E