




- △ PHENOLIC PER MIL-M-14, TYPE CFG, BLACK.
- △ DIALLYL PHTHALATE PER MIL-M-14, TYPE SDG-F, BLUE.
3. MATES WITH BLOCK 201311 AND ACCOMODATES TYPE II, TYPE III+ OR TYPE VI #16 PIN OR SOCKET CONTACTS.

△2	201310-3
△1	201310-1
MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.REIFSNYDER 22 FEB 96		 TE Connectivity			
DIMENSIONS: INCHES		CHK R.STONE 29 FEB 96					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD G.A.STEINHAUER 20 MAR 96	NAME BLOCK, 75 PLACE, MINIATURE RECTANGULAR, M SERIES				
		PRODUCT SPEC —					
		APPLICATION SPEC —					
		WEIGHT .0728 LB					
MATERIAL SEE TABLE	FINISH —	CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C=201310	RESTRICTED TO —
		SCALE 2:1			SHEET 1 of 1	REV AD1	