


5

4

3

2

1



Wire _____ Cu tin plated

Gauge stranded _____ AWG 30 / 7 strands AWG 38

Voltage rating _____ 150 V

Capacitance _____ 83,2 pF/m (single end)

_____ 47,6 pF/m (differential)

Impedance _____ 67 Ω (single end)


_____ 110 Ω (differential)

Conductor resistance _____ 348 mΩ/m

Signal delay _____ 5,31 ns/m

Insulation material _____ PVC

Temperature rating _____ -30°C to +105°C

				Det.	Name	 All Dim. in mm Orig. Size DIN A 4	Flat cable Length per reel : 30,48 m 50 poles, UL 2678	Maßstab/ Scale 8:1
			Detail.	31/05/07	PK			
			Insp.					
			Stand.					
34361	31/05/07	PK	HARTING EURL F-95972 Paris				TB 60 90 050 6008	Blatt/ Page 1 / 1
Mod.	Det.	Name					Sub.	