



T50L2C2

Standard Cable Tie, 15.35" Long, 50lb Tensile Strength, PA66, Red, 100/pkg

Article Number: 111-05457

Part Number: T50L2C2


Type: T50L



Base Data

Part No.	T50L2C2
Type	T50L
Color	Red (RD)
Features	• Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	Used to bundle and secure wire and cable.
Variant	Inside Serrated

Product Dimensions



Min. Tensile Strength	50.0lbs / 225.0N
Length (L)	15.35" / 390.0mm

Width (W) (imperial)	0.18"
Width (W)	4.7mm
Min. Ø Bundle	0.06" / 1.5mm
Max. Ø Bundle	4.3" / 110.0mm

Material and Specifications

Material	Polyamide 6.6 (PA66)
US MILSPEC	MS3367-2-2
Flammability	UL94 V2
Material Specification	RoHS / HF
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	 RoHS
Specification	UL ZODZ2.E64139
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	100
UPC	089306083658

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512