




PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



ROHS PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	Gold Flash	0.76µ Gold
09	30.81	24.99	16.96	16.21	10.96	D09S90C4GX00LF	D09S90C6GX00LF
15	39.14	33.32	25.18	24.54	19.18	D15S90C4GX00LF	D15S90C6GX00LF
25	53.03	47.04	39.12	38.25	33.12	D25S90C4GX00LF	D25S90C6GX00LF
37	69.32	63.50	55.68	54.71	49.68	D37S90C4GX00LF	D37S90C6GX00LF

GENERAL CHARACTERISTICS AND ROHS INFORMATION:

SEE DRAWING C01-8646-0001

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D-SUB					
ltr		ecn no		dr		date		tolerances unless otherwise specified				title			
G		ELX-I-21654		AB		2015-10-26		angles		linear		.0±0.1			
H		ELX-I-24020		AAB		2016-06-06						.00±0.1			
								0°±2'				.000±0.1			
										scale 2:1		FEMALE DELTA-D LOW PROFILE STRAIGHT PRESS-FIT			
								dr		PESSON				1995-04-27	
								engr		MITHUN PAUL				2016-06-06	
								chr		ATHUL A.B				2016-06-06	
								appd		BIJU K PAUL				2016-06-06	
												dwg no			
												sheet 1 of 1			
												size			
												A3			
												type			
												Product Customer Drawing			
sheet index		revision sheet		H		1									