


## Snap Clips

561-1250032, 561-1250062, 561-1250093,  
561-1250125, 561-1560032, 561-1560062,  
561-1560093, 561-1560125, 561-1560156,  
561-1870032, 561-1870062, 561-1870093,  
561-1870125, 561-1870156, 561-1870187,  
561-2190032, 561-2190062, 561-2190093,  
561-2190125, 561-2190156, 561-2190187,  
561-2500032, 561-2500062, 561-2500093,  
561-2500125

Date Last Revised: 05-12-09

### MATERIAL

Natural Nylon 6/6



### Dimensions: in. (mm)

- A combination of Celcon Acetal material, and a resilient body design, give these parts a positive "snap" and a more definite grip when assembled into place
- Designed for other hole sizes from 1/8" to 1/4" and panel thickness from 1/32" to 3/16"

- RoHS Compliant

### SPECIFICATIONS

| Mouser Num. | A   | D      | B             | Hole Size | Panel Thickness | Mouser Num. | A   | D      | B              | Hole Size | Panel Thickness |
|-------------|-----|--------|---------------|-----------|-----------------|-------------|-----|--------|----------------|-----------|-----------------|
| 561-1250032 | .06 | 0.25   | 0.25 (6.35)   | 0.125     | 0.032           | 561-1870156 | .06 | 0.3125 | 0.4375 (11.11) | 0.187     | 0.156           |
| 561-1250062 | .06 | 0.25   | 0.281 (7.14)  | 0.125     | 0.032           | 561-1870187 | .06 | 0.3125 | 0.469 (11.91)  | 0.187     | 0.187           |
| 561-1250093 | .06 | 0.25   | 0.3125 (7.94) | 0.125     | 0.093           | 561-2190032 | .06 | 0.344  | 0.391 (9.93)   | 0.219     | 0.032           |
| 561-1250125 | .06 | 0.25   | 0.344 (8.74)  | 0.125     | 0.125           | 561-2190062 | .06 | 0.344  | 0.422 (10.72)  | 0.219     | 0.062           |
| 561-1560032 | .06 | 0.3125 | 0.281 (7.14)  | 0.156     | 0.032           | 561-2190093 | .06 | 0.344  | 0.453 (11.51)  | 0.219     | 0.093           |
| 561-1560062 | .06 | 0.3125 | 0.3125 (7.94) | 0.156     | 0.062           | 561-2190125 | .06 | 0.344  | 0.484 (12.29)  | 0.219     | 0.125           |
| 561-1560093 | .06 | 0.3125 | 0.344 (8.74)  | 0.156     | 0.093           | 561-2190156 | .06 | 0.344  | 0.516 (13.10)  | 0.219     | 0.156           |
| 561-1560125 | .06 | 0.3125 | 0.375 (9.53)  | 0.156     | 0.125           | 561-2190187 | .06 | 0.344  | 0.547 (13.89)  | 0.219     | 0.187           |
| 561-1560156 | .06 | 0.3125 | 0.406 (10.31) | 0.156     | 0.156           | 561-2500032 | .06 | 0.5    | 0.406 (10.31)  | 0.25      | 0.032           |
| 561-1870032 | .06 | 0.3125 | 0.3125 (7.94) | 0.187     | 0.032           | 561-2500062 | .06 | 0.5    | 0.422 (10.72)  | 0.25      | 0.062           |
| 561-1870062 | .06 | 0.3125 | 0.344 (8.74)  | 0.187     | 0.062           | 561-2500093 | .06 | 0.5    | 0.453 (11.51)  | 0.25      | 0.093           |
| 561-1870093 | .06 | 0.3125 | 0.375 (9.53)  | 0.187     | 0.093           | 561-2500125 | .06 | 0.5    | 0.484 (12.29)  | 0.25      | 0.125           |
| 561-1870125 | .06 | 0.3125 | 0.406 (10.31) | 0.187     | 0.125           |             |     |        |                |           |                 |

Available from Mouser Electronics  
1-800-346-6873 / [www.mouser.com](http://www.mouser.com)

EPD-200447

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.