

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER*	A IN (mm)	B IN (mm)	T IN (mm)	WEIGHT LBS / 100 FT (g)
T12FR-20	.125 (3.2)	.218±.047 (5.5±1.2)	.030±.006 (0.8±0.2)	0.4 (181.4)
T19FR-20	.188 (4.8)	.250±.047 (6.4±1.2)	.032±.008 (0.8±0.2)	0.9 (420.1)
T25FR-20	.250 (6.4)	.375±.047 (9.5±1.2)	.040±.008 (1.0±0.2)	1.1 (499.0)
T38FR-20	.375 (9.5)	.437±.047 (11.1±1.2)	.055±.010 (1.4±0.3)	2.4 (1088.6)
T50FR-20	.500 (12.7)	.500±.047 (12.7±1.2)	.060±.016 (1.5±0.4)	3.6 (1633.0)
T62FR-20	.625 (15.9)	.625±.047 (15.9±1.2)	.062±.020 (1.6±0.5)	4.7 (2131.9)
T75FR-20	.750 (19.1)	.875±.047 (22.2±1.2)	.065±.020 (1.7±0.5)	6.0 (2721.6)
T100FR-20	1.000 (25.4)	1.125±.047 (28.6±1.2)	.070±.020 (1.8±0.5)	8.8 (3991.7)



Notes:

* 1) SEE CURRENT PRICE SHEET FOR PART
NUMBER SUFFIX DESIGNATIONS, PACKAGE
SIZE AND PART COLOR.

B 2) FOR ROLL SIZES LARGER THAN 10 ft.,
SPLICING MAY OCCUR.

3) PART NUMBERS DESIGNATE WITH THE LETTER 'Y' AT THE
END ARE MANUFACTURED FROM A ROHS COMPLIANT MATERIAL.
PART NUMBER EXAMPLE: T50FR-C20Y

A 4) REVERSE CUT



(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS

G03597BK_DC_G00239DO_PB_BLKVOFRWRAP_04

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

BLACK V-O FLAME
RETARDANT SPIRAL WRAP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.XX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

CJG

MAT'L:

POLYETHYLENE

SCALE

NONE

DATE

6/10/96

CHK'D

JVL

DWG NO.

G00239DO

DWG

A

SIZE

4	5/10/11	LEF	VJS	A	ADD NOTE 4 FOR REVERSE CUT B REMOVED PHONE NUMBERS FROM NOTE 2	GB0239DO	4	RAMI	
3	6/4/08	JAD			ADD NOTE 3 FOR ROHS PART NUMBERS	GB0239DO	3		
REV	DATE	BY	CHK		DESCRIPTION	ECN	R	CUST	SUP