




AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 150°c		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20[.008] 3 PLC DEC ± - ANGLES ± -		DR 10-7-93 S.S. GOULDEN CHK 10-7-93 R. HERSEY APPD 10-7-93 B. BARE APPD 10-7-93 M. ELLIS		QTY		PACKAGE TYPE		PART NO		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600 V MAX		MATERIAL COPPER PER ASTM B-152 PVF ² , COLOR:NATURAL		PRODUCT SPEC NOT AVAILABLE		AMP Incorporated Harrisburg, PA 17105-3608					
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 26.65-42.41mm ² [52,600-83,700] STRANDED		FINISH TIN/LEAD (93-7) PER ASTM B545		APPLICATION SPEC NOT AVAILABLE		NAME TERMINAL, RING TONGUE, PVF ² , PLASTI-GRIP, WIRE SIZE:2 AWG					
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.						SIZE B		CAGE CODE 00779		DRAWING NO C-53977	
								WEIGHT -		SCALE NTS		SHEET 1 OF 1			