



Sample photo

**Order symbol:** AL 123608  
**Product nbr:** 7011250  
**Description:** Enclosure  
**Remarks:** Aluminium

**EAN:** 6418074004178  
**El. number:**  
Finland: 3423621  
Denmark: 8212004728  
Italy: 7321060  
Sweden: 2536323

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

| Dimensions:            |  | Length                       | Width | Height | Rating:                                 |
|------------------------|--|------------------------------|-------|--------|-----------------------------------------|
| mm:                    |  | 362                          | 125   | 81     | Ingress Protection (EN 60529): IP 66/67 |
| inch:                  |  | 14.3                         | 4.9   | 3.2    | Impact Resistance (EN 62262): IK 08     |
| Materials:             |  |                              |       |        | NEMA Class: NEMA 1, 4, 4X, 12, 13       |
| Material:              |  | Aluminium                    |       |        | Certificates:                           |
| Base colour:           |  | RAL 7001                     |       |        |                                         |
| Cover colour:          |  | RAL 7001                     |       |        |                                         |
| Cover screws material: |  | Stainless steel              |       |        |                                         |
| Gasket material:       |  | Polyurethane                 |       |        |                                         |
| Temperatures:          |  |                              |       |        |                                         |
| Short term:            |  | -50 ... 140 °C               |       |        |                                         |
| Continuous:            |  | -50 ... 80 °C                |       |        |                                         |
| Short term:            |  | -60 ... 285 °F               |       |        |                                         |
| Continuous:            |  | -60 ... 175 °F               |       |        |                                         |
| Accessories:           |  |                              |       |        |                                         |
| AM 1212                |  | Mounting plate               |       |        |                                         |
| AM 1222                |  | Mounting plate               |       |        |                                         |
| AM 1236                |  | Mounting plate               |       |        |                                         |
| ARH 12                 |  | DIN-35 Mounting rail         |       |        |                                         |
| ARH 36                 |  | DIN-35 Mounting rail         |       |        |                                         |
| MR 75005               |  | Selftapping taptite screw M5 |       |        |                                         |
| MRS 28541              |  | Wall fastening lug (2 pcs)   |       |        |                                         |
| PH A & AH A/B          |  | Hinge set                    |       |        |                                         |

