

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0870310625

Status:

Obsolete

Overview:

[modular_plugs_jacks](#)

Description:

Modular Plug, Short Body, 6/2

Documents:

[Drawing \(PDF\)](#)

Agency Certification

UL

E107635

General

Product Family

Modular Jacks/Plugs

Series

87031

Component Type

Wire Plug

Magnetic

No

Obsolete Date

2004/01/01

Overview

[modular_plugs_jacks](#)

Performance Category

3

Power over Ethernet (PoE)

N/A

Product Name

RJ11

Physical

Flammability

94V-2

Inverted / Top Latch

N/A

Lightpipes/LEDs

None

Material - Metal

Phosphor Bronze

Orientation

N/A

PCB Retention

None

Packaging Type

Bag

Positions / Loaded Contacts

6/2

Surface Mount Compatible (SMC)

N/A

Temperature Range - Operating

-40°C to +60°C

Wire/Cable Type

Flat Oval

Electrical

Current - Maximum per Contact

1.5A

Grounding to Panel

N/A

Shielded

No

Voltage - Maximum

125V

Solder Process Data

Replacement RoHS Compliant Part Number

None

Material Info

EU RoHS

Not RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

87031Series

Mates With

FCC 68 Jacks

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

IDT - Manual Press

0011201272

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION