

40mm sq.**San Ace 40****General Specifications**

- Material.....Frame: Plastics (Flammability: UL94V-0),
Impeller: Plastics (Flammability: UL94V-0)
- Expected LifeRefer to specifications (L10: Survival rate: 90% at 60°C ,
rated voltage, and continuously run in a free air state)
- Lead Wire⊕red ⊖black (Sensor) yellow (Control) brown
- Storage Temperature ...-30°C to +70°C (Non-condensing)


40×40×28mm [Mass : 53g] **9GA type** **Low Power Consumption Fan****Specifications** The following nos. **have PWM controls, pulse sensors, and ribs.** For ribless, append "1" to the model no.

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	PWM duty cycle* [%]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Airflow [m ³ /min] [CFM]	Max. Static Pressure [Pa] [inchH ₂ O]	SPL [dB(A)]	Operating Temperature [°C]	Expected Life [h]
9GA0412P3K01	12	10.8 to 13.2	100	0.92	11.04	22,000	0.81 28.6	799 3.21	61	-20 to +60	30,000/60°C
			0	0.10	1.2	6,500	0.23 8.12	68 0.27	32		
9GA0412P3J01			100	0.49	5.88	18,000	0.67 23.7	535 2.15	54	-20 to +70	40,000/60°C
			0	0.05	0.6	4,500	0.16 5.7	33 0.13	22		
9GA0412P3G01			100	0.39	4.68	16,500	0.61 21.5	450 1.81	53		
			0	0.05	0.6	4,500	0.16 5.7	33 0.13	22		
9GA0412P3H01			100	0.28	3.36	14,500	0.54 19.1	347 1.39	50		
			0	0.04	0.48	3,500	0.13 4.6	20 0.08	17		
9GA0412P3M01			100	0.21	2.52	12,500	0.46 16.2	258 1.04	47		
			0	0.04	0.48	3,500	0.13 4.6	20 0.08	17		
9GA0424P3J001 ^(Note)		24	100	0.27	6.48	18,000	0.67 23.7	535 2.15	54		
9GA0424P3G001 ^(Note)			100	0.22	5.28	16,500	0.61 21.5	450 1.81	53		
9GA0424P3H001 ^(Note)			100	0.16	3.84	14,500	0.54 19.1	347 1.39	50		
9GA0424P3M001 ^(Note)			100	0.11	2.64	12,500	0.46 16.2	258 1.04	47		


Note: Rated voltage 24V fans do not rotate when PWM duty cycle is 0%.

※PWM Frequency : 25kHz

Other sensor specifications are available as options. Please refer to the index (p. 504).

Dimensions (unit: mm) (With ribs)

Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)




Options (unit: mm)

Finger Guards

Model : 109-059
: 109-059H


Surface treatment : Nickel-chrome plating (silver)
: Cation electropainting (black)

Color




Airflow - Static Pressure Characteristics


PWM Duty Cycle



9GA0412P3K01




9GA0412P3J01




9GA0412P3G01


Operating Voltage Range



9GA0412P3K01




9GA0412P3J01




9GA0412P3G01


PWM Duty - Speed Characteristics Example












9GA0412P3K01












9GA0412P3J01



9GA0412P3G01

40mm sq.**San Ace 40****40×40×28mm** [Mass : 53g]**Airflow - Static Pressure Characteristics****PWM Duty Cycle****9GA0412P3H01****9GA0412P3M01****9GA0424P3J001****Operating Voltage Range****9GA0412P3H01****9GA0412P3M01****9GA0424P3J001****PWM Duty - Speed Characteristics Example****9GA0412P3H01****9GA0412P3M01****9GA0424P3J001**

**9GA0424P3G001****9GA0424P3H001****9GA0424P3M001****9GA0424P3G001****9GA0424P3H001****9GA0424P3M001****9GA0424P3G001****9GA0424P3H001****9GA0424P3M001**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sanyo Denki:

[9GA0412P3J011](#) [9GA0424P3H001](#) [9GA0424P3J001](#) [9GA0424P3J0011](#) [9GA0424P3M0011](#) [9GA0424P3M001](#)
[9GA0424P3H0011](#) [9GA0424P3G0011](#) [9GA0424P3G001](#) [9GA0412P3G01](#) [9GA0412P3G011](#) [9GA0412P3H01](#)
[9GA0412P3H011](#) [9GA0412P3J01](#) [9GA0412P3M01](#) [9GA0412P3M011](#) [9GA0412P3K01](#) [9GA0412P3K011](#)