

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982660300](#)
Status: **Active**
Overview: [Premo-Flex Cable Jumpers](#)
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 102.00mm Cable Length, Tin (Sn) Plating, 28 Circuits



Series image - Reference only

Documents:

- | | |
|--|--|
| Drawing (PDF) | Datasheet (PDF) |
| Product Specification PS-98266-001-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Packaging Specification PK-98266-001-001 (PDF) | |

General

Product Family	Cable
Series	98266
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	Premo-Flex Cable Jumpers
Product Name	Premo-Flex FFC Jumper
UPC	756054772560

Physical

Cable Length	102.00mm
Circuits (Loaded)	28
Material - Plating Mating	Tin
Net Weight	0.943/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-98266-001-001
Product Specification	PS-98266-001-001
Sales Drawing	SD-98266-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[98266](#) Series

Mates With

Easy-On FFC/FPC Connector:

[524352833](#) , [524372833](#) , [525592833](#) ,
[525592834](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION