



NVDQ900-2

NVQ900-22

NVQ900-22 NVDQ900-2

The 900 series sets an entirely new standard in design and construction of industrial vacuum cleaners, built by professionals to ensure high performance coupled with reliability and long service life.

The exciting use of Structofoam throughout this machine really makes it as strong as a truck, whilst its innovative design makes it every bit as easy to use as smaller machines. Power and performance are to the full Twinflo' specification and there is a choice of one or two-motored models with a dual 2-stage primary filter system as standard.

The rugged container is classic Structofoam engineering and the giant wheels and heavy-duty castors provide excellent mobility and transit even in the most demanding applications.

The standard 38mm (1 1/2") accessory kit includes our extra long double swivel hose; stainless steel tubes; 400mm (16") Structofoam floor nozzle and additional useful accessories.

The innovative yet thoroughly practical design of the 900's is really different, but it is that difference that really counts.

Model	Motor	Power	Airflow	Suction	Cap	Range	Weight	Dimensions
NVQ	1200W	230V	45 L/sec	2600mm	40L	26.8m	22.5Kgs	800 x 490
NVDQ	2400W	AC 50/60Hz	90 L/sec	2600mm	40L	26.8m	25.0Kgs	x 880mm

Also available 115V/120V specification.