


entrelec

terminal blocks

clamp
DIN 1 - 3

M 16/12...

Spacing 12 mm - 0,1 (.473")

Standard 12 mm block
with partition.

0115 129.14

Standard blocks

Grey	M 16/12	0115 129.14
Blue	M 16/12.N	0125 129.16
Yellow	M 16/12	0105 129.23
Beige V0	M 16/12.V0	0195 129.15
Blue V0	M 16/12.N.V0	0199 005.21

149-298

Accessories

1	End section	grey	FEM12	th. 3,0 mm	0118 618.01
		blue	FEM12	th. 3,0 mm	0128 618.03
		yellow	FEM12	th. 3,0 mm	0103 065.24
		beige	FEM12 V0	th. 3,0 mm	0198 618.02
		blue	FEM12 V0	th. 3,0 mm	0199 303.00
2	Separator end section	grey	SCF12	th. 3,0 mm	0118 102.10
		beige	SCF12 V0	th. 3,0 mm	0193 102.11
3	Separator end section	grey	SCFM6	th. 3,0 mm	0114 825.05
4	Separator end section	grey	SCFEX1	th. 2,4 mm	0109 619.04
5	Separator end section	grey	SCFEX3	th. 2,4 mm	0103 620.01
6	Separator end section for cover CPV	grey	SCFCV1.2	th. 2,0 mm	0118 795.11
		beige	SCFCV1.2 V0	th. 2,0 mm	0198 795.12
7	Protective cover		CPM	(for SCF12... SCFM6)	0187 312.14
8	Protective cover		CPV1.2	(for SCFCV1.2)	0118 818.12
9	Test socket		AL2	DIA. 2,0 mm	0163 043.21
			AL3	DIA. 3,0 mm	0163 261.00
			AL4	DIA. 4,0 mm	0163 262.01
10	Test plug		FC2	DIA. 2,0 mm	0197 885.28
			FC4	DIA. 4,0 mm	0197 890.01
11	Assembled jumper bar	76 A	BJM 12	2 poles	0179 618.16
		76 A	BJM 12	3 poles	0179 619.17
				4 poles	0179 620.14