


MICRO SWITCH
a Honeywell Division

FED.MFG.CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-3RW8221555112D6S




NOTE
(1) MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF Ø.165 MAX ON 1.000 ±.002 CENTERS

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 6.5 OZ MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE — — — 1.5 OZ MIN	L9	ONE PLACE (.0)	±.030
DIFFERENTIAL TRAVEL — — — .007-.030	10A 125, <u>250</u> OR 480 VAC 1/2A 125 VDC, 1/4A 250 VDC	TWO PLACE (.00)	±.015
OVERTRAVEL — — — .094 MIN	L288	THREE PLACE (.000)	±.005
	CE  	ANGLES	±
		WEIGHT .076 LB	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[SCN-2417SC](#)