

PermaSleeve® Wire Marking Sleeves

www.BradyID.com

3" Core Wire & Cable Materials:

B-345 PermaSleeve® Double-Sided High Temperature PVDF Wire Marking Sleeves:

Use the table below to browse all available double-sided printing, 2" width B-345 PermaSleeve® HT High Temperature PVDF Wire Marking Sleeves or build your own catalog number on page 170.

Double-Sided Printable, 2" Sleeve Width

Catalog #	Color	Sleeves Per Roll	Approx. Wire Gauge	Range of Wire Diameter Inch (mm) Min. Max.	Supplied Diameter Inch (mm)	Recovered Diameter Inch (mm)	Recovered Wall Thickness Inch (mm)	Sleeve Width Inch (mm)	Rec. Printer	Rec. Ribbon
3HT-094-2-WT-S	White	500	26 to 20	0.031 (0.8) - 0.080 (2.0)	0.094 (2.4)	0.031 (0.8)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
3HT-094-2-WT-S**	White	500	26 to 20	0.031 (0.8) - 0.080 (2.0)	0.094 (2.4)	0.031 (0.8)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-125-2-WT-S	White	500	20 to 16	0.063 (1.6) - 0.110 (2.8)	0.125 (3.2)	0.062 (1.6)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-125-2-WT-S**	White	500	20 to 16	0.063 (1.6) - 0.110 (2.8)	0.125 (3.2)	0.062 (1.6)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-187-2-WT-S	White	500	16 to 10	0.094 (2.4) - 0.150 (3.8)	0.187 (4.7)	0.093 (2.4)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-187-2-WT-S**	White	500	16 to 10	0.094 (2.4) - 0.150 (3.8)	0.187 (4.7)	0.093 (2.4)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-250-2-WT-S	White	500	12 to 8	0.125 (3.2) - 0.215 (5.5)	0.250 (6.4)	0.125 (3.2)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-250-2-WT-S**	White	500	12 to 8	0.125 (3.2) - 0.215 (5.5)	0.250 (6.4)	0.125 (3.2)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-375-2-WT-S	White	250	8 to 4	0.187 (4.7) - 0.320 (8.1)	0.375 (9.5)	0.187 (4.7)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-375-2-WT-S**	White	250	8 to 4	0.187 (4.7) - 0.320 (8.1)	0.375 (9.5)	0.187 (4.7)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-500-2-WT-S	White	250	6 to 1	0.250 (6.4) - 0.450 (11.4)	0.500 (12.7)	0.250 (6.4)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-500-2-WT-S**	White	250	6 to 1	0.250 (6.4) - 0.450 (11.4)	0.500 (12.7)	0.250 (6.4)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-750-2-WT-S	White	100	2 to 4/0	0.375 (9.5) - 0.700 (17.8)	0.750 (19.0)	0.375 (9.5)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-750-2-WT-S**	White	100	2 to 4/0	0.375 (9.5) - 0.700 (17.8)	0.750 (19.0)	0.375 (9.5)	0.015 (0.4) ± 0.003 (0.07)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-1000-2-WT-S	White	100	2/0 to 0.950 dia.	0.450 (11.4) - 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.017 (0.4) ± 0.004 (0.1)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-1000-2-WT-S**	White	100	2/0 to 0.950 dia.	0.450 (11.4) - 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.017 (0.4) ± 0.004 (0.1)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-1000-2-WT-S	White	100	2/0 to 0.950 dia.	0.450 (11.4) - 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.017 (0.4) ± 0.004 (0.1)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602
2HT-1000-2-WT-S**	White	100	2/0 to 0.950 dia.	0.450 (11.4) - 0.950 (24.1)	1.000 (25.4)	0.500 (12.7)	0.017 (0.4) ± 0.004 (0.1)	2.000 (50.8)	PR Plus, BBP72, IP	R6002/ R6602

*Choosing Your PermaSleeve Color

While white is a standard color, additional colored sleeves are available as stock parts as well. Simply replace "WT" with the abbreviation of the desired color to order.

Example: 2HT-094-2-WT-S becomes 2HT-094-2-YL-S

Available Stock Colors:

WT = White BL = Blue YL = Yellow
BK = Black PK = Pink

** Choosing Your PermaSleeve Pieces (optional):

While 1 or 2 markers per sleeve is standard, you may also choose to have each sleeve slit multiple times to produce multiple pieces. Simply replace the double asterisks (**) in the catalog number to fill in your desired pieces per marker.

Example: 2HT-187-2-WT-S** becomes 2HT-187-2-WT-S-4


This "4" means that this 2.000" sleeve is slit into four 0.500" pieces.

Standard Options:

1 or 2 markers per sleeve

Other Available Slit Options:

3 or 4 markers per sleeve
(Contact Brady Customer Service for availability)



Approx. wire gauge based on AWG for THHN wire.

View the Material Brands & Attributes Guide on page 4.

Benchtop Printer Ribbons on page 184.

Full Material Properties on page 187.

1-888-272-3946 | www.BradyID.com