


CABLE MARKERS

141-575
to
141-584

PRODUCT DATA



Z-TYPE MARKERS (Straight and Chevron Cut)

For cable diameter mm	For cable size* mm² (BS6004)	Marker size	Marker length mm	Packed Reel Box	Order code (Straight cut)	Order code (Chevron cut)
1.5-2.0	—	5	4.5	1000	0580	1151
2.0-3.2	1.0	7	4.5	1000	0581	1152
2.5-4.0	1.5	9±	4.5	1000	0615	1153
2.9-4.7	2.5	11	4.5	1000	0616	1154
3.4-5.7	4.0	13±	4.5	1000	0617	1155
3.8-6.3	6.0	15	4.5	1000	0618	1156
4.3-6.9	10.0	18	4.5	500	0620	1157
5.5-8.9	16.0	23±	6.0	500	0622	1158
7.9-12.7	25.0	35	6.0	250	0624	1159

*Application to cables BICC Ref. No. 6491X ± Available green stripe earth (straight cut only)

COLOUR OPTIONS (STRAIGHT CUT)

White body marked black:

A-Z, 0-9 and symbols, available in Reel pack (R) and Box pack (A)

Yellow body marked black:

A-Z, 0-9 and symbols, available in Reel pack only
Size 9, 13 and 23 available striped Green/Yellow with earth symbol

COLOUR OPTION (CHEVRON CUT)

White Body marked black.

A-Z, 0-9 and symbols, available in box pack (A) only

Yellow body marked black:

A-Z, 0-9 and symbols, Available in reel pack (R) only

COLOUR CODED

0-9 Available in box pack (A) only (Reels subject to quotation)

SPECIAL MARKINGS

Z-Type markers are available with up to 4 characters, subject to special quotation

MATERIAL

PPVC

SERVICE TEMPERATURE RANGE

-45°C to +70°C

CHEMICAL RESISTANCE

(24 hours @ various temp.)

Excellent: Aircraft Fuel, Propan-2-ol, 1,1,1 Trichloroethane, Kilfrost, Silicone Hydraulic Fluid
Good: Aeroshell (4), Sullage Fluid, Gas Turbine Oil 98
Poor: Skydrol 500 B4



K-TYPE MARKERS

For cable diameter mm	For cable size mm² (BS6004)	Marker size	Marker length mm	Packed Reel (R)	Order code
4.2-7.0	4.0-10.0	65±	6.0	500	1361

*Application to cables BICC Ref. No. 6491X ± Available with white body marked black

STANDARD COLOUR

Yellow body marked black, A-Z, 0-9 and symbols

COLOUR CODED

0-9 only, available in reel pack only

MATERIAL

PPVC

SERVICE TEMPERATURE RANGE

-45°C to +70°C

CHEMICAL RESISTANCE

(24 hours @ various temp.)

Excellent: Aircraft Fuel, Silicone Hydraulic Fluid, Propan-2-ol, Kilfrost Fluid, 1,1,1 Trichloroethane, Petrol, 50% Sodium Chloride, White Spirit, Tap Water, Sea Water,

10% Detergent Solution, Diesel Fuel, Diala Oil B, Diethyl Ether, Ammonium Hydroxide

Good: Aeroshell (4), Sullage Fluid, Gas Turbine Oil 98, Methanol, 20% Sodium Hydroxide

Poor: Skydrol 500 B4, Hydrochloric Acid, Acetone



C-TYPE MARKERS

For cable diameter mm	For cable size mm² (BS6004)	Marker size	Marker length mm	Packed Box (A)	Order code
2.1-2.5	—	2	4.0	1000	0594
2.5-3.0	1.0	3	4.0	1000	0595
3.0-3.5	1.5	4	4.0	1000	0596
3.5-4.0	—	5	4.0	1000	0597
4.0-4.8	2.5	6	6.0	1000	0598
4.8-5.5	4.0 & 6.0	7	6.0	500	0599
5.5-6.3	—	8	6.0	500	0600
6.3-7.0	10.0	9	6.3	500	0601
7.0-7.9	—	10	6.3	250	0602
7.9-8.8	16.0	11	6.3	250	0603
8.8-10.0	25.0	12	6.3	250	0660
10.0-11.5	35.0	13	6.3	250	0661
11.5-12.6	—	14	6.3	250	0662
12.6-14.5	50.0	15	6.3	250	0663

*Application to cables BICC Ref. No. 6491X

STANDARD COLOURS

White body marked black

MATERIAL

PVC

SERVICE TEMPERATURE RANGE

-25°C to +50°C

CHEMICAL RESISTANCE

Excellent: Aeroshell (4), Propan-2-ol, Silicone Hydraulic Fluid, Aircraft Fuel, Ammonium Hydroxide, Methanol, Sea Water, Tap Water, 50% Sodium Chloride, Diala Oil B, 20% Sodium Hydroxide, 10% Detergent Solution, Diethyl Ether, Diesel Fuel

Good: Gas Turbine Oil 98, Sullage Fluid, 1,1,1 Trichloroethane, White Spirit, Hydrochloric Acid, Petrol, Concentrated Nitric Acid

Poor: Acetone, Skydrol 500 B4