






METRIC

THIRD ANGLE
PROJECTION




DO NOT SCALE

DIMENSIONS IN mm

REVISIONS

LTR	DESCRIPTION	DATE	DWN	APVD
A1	REV PER ECO-09-022178	25SEP09	KK	AEG



OPTIONAL

SLOT ACCEPTS
27-25 AWG COPPER
MAGNET WIRE EITHER
SINGLE OR DOUBLE
OF THE SAME SIZE.

1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

1 OBSOLETE		TIN PLATED	L.P. MADE OF 160809-2	160809-4
		TIN PLATED	BRASS	160809-2
		FINISH	MATERIAL	PART NUMBER
CUSTOMER DRAWING		AMP AMP-HOLLAND B.V. 's-Hertogenbosch, The Netherlands		
FOR REFERENCE ONLY WILL NOT BE UPDATED		THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION 3 APRIL 1986 © COPYRIGHT 1985 BY AMP-HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.		
DR. D. CAMPSCHRODER NOVEMBER 1985		WIRE RANGE 27-25 AWG	NAME MAG MATE 4,75 WITH TAB 2.8	REV. DATE D M Y. 3 4 86
CHK. AEG DATE 25/09/09		INSUL. RANGE		
APP. 7.2.86		SIZE A3	SHEET 1 OF 1	DRAWING NO C 160809
				REV. LTR. A1