



Part Number: 74573-2112

Image not available

Status: Active - Custom
Series: 74573
Category: Cable Assemblies
Overview: iPass™

Series image - Reference only

Mates With Part(s):

[75783](#) iPass™ Right Angle Connector
[75784](#) iPass™ Vertical Connector

Product Environmental Compliance

[EU RoHS](#): ELV and RoHS Compliant

[China RoHS](#):

[REACH SVHC](#):

[Low-Halogen Status](#): Not Reviewed

Part Detail

General

Status	Active - Custom
Category	Cable Assemblies
Series	74573
Connector to Connector	Mini SAS-to-Mini SAS
Overview	iPass™
Product Name	iPass™, SAS

Physical

Cable Length	0.50m
Circuits (Loaded)	36
Color - Resin	Black, Natural
Gender	Male-Male
Lock to Mating Part	Yes
Material - Resin	Low Density Polyethylene, Polyester
Packaging Type	Bag
Pitch - Mating Interface	0.80mm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	N/A
Wire Size AWG	30
Wire/Cable Type	Twin-ax

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Shielded	Yes
Voltage - Maximum	30V AC

Material Info

UPC	822350625012
-----	--------------

Reference - Drawing Numbers

Sales Drawing	SD-74573-210
---------------	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

