

60mm sq.**San Ace 60L**



25mm thick

**General Specifications**

- Material Frame: Aluminum, Impeller: Plastics (Flammability: UL94V-1)
- Expected Life Refer to specifications (L10:Survival rate: 90% at 60°C , rated voltage, and continuously run in a free air state)
- Lead Wire ⊕red ⊖black or blue (Sensor) yellow
- Storage Temperature -30°C to +70°C (Non-condensing)

60×60×25mm [Mass : 100g]**Specifications** The following nos. **have pulse sensors.**


Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Air Flow [m ³ /min] [CFM]	Max. Static Pressure [Pa] [inchH ₂ O]	SPL [dB(A)]	Operating Temperature [°C]	Expected Life [h]
109L0612G401	12	10.2 to 13.8	0.24	2.88	5,600	0.78	27.5	87.3	- 20 to + 70	100,000
109L0612S401			0.17	2.04	4,600	0.65	23.0	56.8		
109L0612H401			0.11	1.32	3,800	0.53	18.7	40.2		
109L0612F401			0.09	1.08	3,200	0.44	15.5	29.4		
109L0612M401			0.06	0.72	2,600	0.36	12.7	19.6		
109L0624D401	24	20.4 to 27.6	0.12	2.88	5,150	0.72	25.4	73.8		
109L0624S401			0.08	1.92	4,600	0.65	23.0	56.8		
109L0624H401			0.06	1.44	3,800	0.53	18.7	40.2		
109L0624F401			0.05	1.20	3,200	0.44	15.5	29.4		
109L0624M401			0.04	0.96	2,600	0.36	12.7	19.6		
109L0648G401	48	40.8 to 55.2	0.07	3.36	5,600	0.78	27.5	87.3	- 20 to + 60	80,000
109L0648H401		40 to 53	0.04	1.92	3,800	0.53	18.7	40.2	- 20 to + 70	100,000

Available options: ⇒ **Without Sensor**Please inquire as the availability of these functions depend on the model. ⇒ **Lock Sensor** **Low speed Sensor****Dimensions (Unit : mm)****Reference dimension of mounting holes and vent opening (Unit : mm)****Options (Unit : mm)****Finger guards**

Model : 109-139E Surface treatment : Nickel-chrome plating (silver)
 : 109-139H : Cation electropainting (black)

Resin Finger guards

Model : 109-1003G



Options (Unit : mm)

Resin filter kits

Model : 109-1003F13 (13PPI), 109-1003F20 (20PPI)
: 109-1003F30 (30PPI), 109-1003F40 (40PPI)



Air Flow - Static Pressure Characteristics



109L0612G401



109L0648G401



109L0624D401



109L0612S401

109L0624S401



109L0612H401

109L0624H401



109L0648H401



109L0612F401

109L0624F401



109L0612M401

109L0624M401

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sanyo Denki:

[109L0612F401](#) [109L0612F402](#) [109L0612F4D01](#) [109L0612G401](#) [109L0612G402](#) [109L0612G4D01](#) [109L0612H401](#)
[109L0612H402](#) [109L0612H4D01](#) [109L0612M401](#) [109L0612M402](#) [109L0612M4D01](#) [109L0612S401](#)
[109L0612S402](#) [109L0612S4D01](#) [109L0624F401](#) [109L0624F402](#) [109L0624F4D01](#) [109L0624H401](#) [109L0624H402](#)
[109L0624H4D01](#) [109L0624M401](#) [109L0624M402](#) [109L0624M4D01](#) [109L0624S401](#) [109L0624S402](#)
[109L0624S4D01](#) [109L0648G401](#) [109L0648G4D01](#) [109L0648H401](#) [109L0648H402](#) [109L0648H4D01](#)
[109L0648S4D01](#)