



My Cart |



My Part Lists |



Sign In/Register



English (Change)

Have a Question?
Chat with a Product
Information Specialist



What can we help you find?



Products

Industries

Resources

About TE

My Account

Innovation

Support Center


Home > Products > Terminals & Splices > Product Feature Selector > Product Details

880683-1 Product Details

Share

Print

Email



880683-1

TE Internal Number: 880683-1

Active

View 3D PDF

FASTON Uninsulated Receptacles & Housings



Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Terminal
- Terminal Type = Receptacle
- Mating Area Interface Dimensions = 6.35 mm
- Board Mount = No
- Receptacle Style = Straight

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [TERMINAL FASTON .250 REC. \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- [None Available](#)

Product Specifications:

- [None Available](#)

Application Specifications:

- [None Available](#)

Instruction Sheets:

- [None Available](#)

CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing \(DXF, Version A1\)](#)
- [3D Model \(IGES, Version A1\)](#)
- [3D Model \(STEP, Version A1\)](#)

[List all Documents](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Terminal
- Terminal Type = Receptacle
- Receptacle Style = Straight
- Insulation Support = Insulation Support
- Wire/Cable Type = Stranded
- Insertion Force = Normal
- Finish = None

Mechanical Attachment:

- Board Mount = No

Termination Features:

- Crimp Type = F-Crimp

Dimensions:

- Mating Area Interface Dimensions (mm [in]) = 6.35 [.250]
- Insulation Diameter (mm [in]) = 2.00-3.30 [.079-.130]

Body Features:

- Weld Tab = Without
- Wire Range (mm [AWG]) = 0.50-1.00² [20-17]
- Material = Brass

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- For Hermetic Header Tab = No

Packaging Features:

- Packaging Method = Reel

Other:

- Line = Budget
- Brand = TE Connectivity

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

