




注記 NOTE

1. 嵌合相手 : 505570シリーズ
MATING WITH:505570SERIES
2. エンボス梱包品の詳細は5055780001PSD001を参照
DETAILED TAPING PACKAGE, SEE 5055780001PSD001.
3. アプリケーション仕様書 (コネクタ取扱い説明書)
: 5055700001PSA02, 5055700001PSA03
APPLICATION SPECIFICATION(CONNECTOR MANUAL)
: 5055700001PSA02, 5055700001PSA03
4. 製品仕様書:5055700001PS001
PRODUCT SPECIFICATION:5055700001PS001


5.製品番号 MATERIAL No.

505578**7*

極数	色	No.	COLOR
CIRCUIT SIZE	COLOR	0	NATURAL
		1	BLACK

6.ターミナルとネイルの平坦度は0.1mm以下
 TERMINAL AND NAIL COPLANARITY:0.1mm MAX.


7.ELV & RoHS 適合品
ELV & RoHS COMPLIANT





30.0	14.0	34.53	30.0	36	5055781671	5055781670	16
28.0	14.0	32.53	28.0	34	5055781571	5055781570	15
26.0	14.0	30.53	26.0	32	5055781471	5055781470	14
24.0	14.0	28.53	24.0	30	5055781371	5055781370	13
22.0	14.0	26.53	22.0	28	5055781271	5055781270	12
20.0	14.0	24.53	20.0	26	5055781171	5055781170	11
18.0	10.0	22.53	18.0	24	5055781071	5055781070	10
16.0	10.0	20.53	16.0	22	5055780971	5055780970	9
14.0	10.0	18.53	14.0	20	5055780871	5055780870	8
12.0	10.0	16.53	12.0	18	5055780771	5055780770	7
10.0	10.0	14.53	10.0	16	5055780671	5055780670	6
8.0	5.5	12.53	8.0	14	5055780571	5055780570	5
6.0	5.5	10.53	6.0	12	5055780471	5055780470	4
4.0	3.5	8.53	4.0	10	5055780371	5055780370	3
2.0	3.5	6.53	2.0	8	5055780271	5055780270	2
E	D	C	B	A	ハウジング 黒色 HSG COLOR BLACK	ハウジング ナチュラル HSG COLOR NATURAL	極数 CIRCUIT
					エンボス梱包 オーダー番号 EMBOSSED PKG ORDER No.		

No.	部品 PART	材質 MATERIAL
①	ハウジング HOUSING	ポリアミド(PA) UL94 V-0 POLYAMIDE(PA) UL94 V-0 色：ナチュラル、黒 COLOR:NATURAL, BLACK
②	ターミナル TERMINAL	黄銅 BRASS
		錫めっき：1.0um以上 MATTE TIN PLATING：1.0 micro-meter MIN.
		ニッケルめっき（下地）：1.0um以上 NICKEL(UNDER PLATING)：1.0micro-meter MIN
③	フィッティングネイル FITTING NAIL	リン青銅 PHOSPHOR BRONZE
		錫めっき：1.0um以上 MATTE TIN PLATING：1.0 micro-meter MIN.
		ニッケルめっき（下地）：1.0um以上 NICKEL(UNDER PLATING)：1.0micro-meter MIN





THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

RELEASED EC NO: 105541 DRWN: TENAGASE CHK'D: KOMURAKAMI APPR: TKANEKO	2016/05/12	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 3.0 ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.2 1 PLACE ± 0.25 0 PLACES ± 0.3 DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION UNITS MM	SCALE 5:1	molex® MICRO-LOCK PLUS 2.0MM PITCH WIRE TO BOARD PLUG ASSEMBLY RA				
	2016/06/23		DRWN BY TENAGASE	DATE 2016/05/12					
	2016/06/23		CHK'D BY KOMURAKAMI	DATE 2016/06/23	PRODUCT CUSTOMER DRAWING				
	2016/06/23		APPR BY TKANEKO	DATE 2016/06/23					
	REV		DRAWING SIZE A3	THIRD ANGLE PROJECTION 	SERIES 505578	MATERIAL NUMBER	CUSTOMER GENERAL		
	A				DOCUMENT NUMBER 5055780001	DOC TYPE PSD	DOC PART 000	SHEET NUMBER 1 OF 2	

ロック形状
LOCK FORM




吸着エリア
PICK UP AREA



基板パターンレイアウト (参考)
P.W.B. PATTERN LAYOUT (REFERENCE)

(メタルマスク厚み150um,開口率100%)
(METAL MASK THICKNESS150um,OPEN APERTURE RATIO100%)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																				
RELEASED	EC NO: 105541 DRWN: TENAGASE CHK'D: KOMURAKAMI APPR: TKANEKO	2016/05/12 2016/06/23 2016/06/23	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®											
					MM		5:1													
			ANGULAR TOL ± 3.0 °		DRWN BY		DATE		MICRO-LOCK PLUS 2.0MM PITCH WIRE TO BOARD PLUG ASSEMBLY RA											
					TENAGASE		2016/05/12													
			4 PLACES	±	CHK'D BY		DATE								PRODUCT CUSTOMER DRAWING					
			3 PLACES	±	KOMURAKAMI		2016/06/23													
			2 PLACES	± 0.2	APPR BY		DATE		SERIES 505578											
			1 PLACE	± 0.25	TKANEKO		2016/06/23								MATERIAL NUMBER				CUSTOMER GENERAL	
	0 PLACES	± 0.3																		
	A	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DRAWING SIZE		THIRD ANGLE PROJECTION												
A3																				
					DOCUMENT NUMBER				DOC TYPE		DOC PART		SHEET NUMBER							
					5055780001				PSD		000		2 OF 2							

