

PRODUCT SPECIFICATION

CKI: Carl Kammerling International Ltd.

Brand	C.K
Product Range	SensoPlus Screwdrivers
Catalogue number	490
Date	29/11/2006

Range Description A range of Professional quality screwdrivers		 		
Features • Ergonomic dual compound handle offering the perfect balance of grip and comfort • Non roll handle design – Specifically designed to stop the screwdrivers rolling off non flat surfaces • Contoured blade insulation for improved terminal access • Permanent tip type marking on the end of the handle for convenient blade type identification • Additional blade type identification with colour coded handles • Toughened high alloy steel blade offering the ultimate in wear resistance and performance • Blade torque capacity up to 20% over the International standards requirement • Chrome plated shaft with black non peel tip finish for corrosion protection • Precision machined tips for the ultimate screw fit and high torque output				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
T49010 075	SensoPlus Flared Tip Screwdriver, Slotted, 4.0 x 75mm	5013969979923	82054000	6
T49010 100	SensoPlus Flared Tip Screwdriver, Slotted, 5.5 x 100mm	5013969979930	82054000	6
T49010 125	SensoPlus Flared Tip Screwdriver, Slotted, 6.5 x 125mm	5013969979947	82054000	6
T49010 150	SensoPlus Flared Tip Screwdriver, Slotted, 6.5 x 150mm	5013969979954	82054000	6
T49010 175	SensoPlus Flared Tip Screwdriver, Slotted, 8.0 x 175mm	5013969979961	82054000	6
T49010 200	SensoPlus Flared Tip Screwdriver, Slotted, 10.0 x 200mm	5013969979978	82054000	6

T49012 0	SensoPlus Screwdriver PH 0 x 60mm	5013969979985	82054000	6
T49012 1	SensoPlus Screwdriver PH 1 x 80mm	5013969979992	82054000	6
T49012 2	SensoPlus Screwdriver PH 2 x 100mm	5013969980011	82054000	6
T49012 3	SensoPlus Screwdriver PH 3 x 150mm	5013969980028	82054000	6
T49013 0	SensoPlus Screwdriver PZD/SDV 0 x 60mm	5013969980035	82054000	6
T49013 1	SensoPlus Screwdriver PZD/SDV 1 x 80mm	5013969980042	82054000	6
T49013 2	SensoPlus Screwdriver PZD/SDV 2 x 100mm	5013969980059	82054000	6
T49013 3	SensoPlus Screwdriver PZD/SDV 3 x 150mm	5013969980066	82054000	6
T49017 06	SensoPlus Screwdriver TX 06 x 50mm	5013969985658	82054000	6
T49017 07	SensoPlus Screwdriver TX 07 x 50mm	5013969985665	82054000	6
T49017 08	SensoPlus Screwdriver TX 08 x 70mm	5013969980073	82054000	6
T49017 09	SensoPlus Screwdriver TX 09 x 70mm	5013969980080	82054000	6
T49017 10	SensoPlus Screwdriver TX 10 x 80mm	5013969980097	82054000	6
T49017 1030	SensoPlus Screwdriver TX 10 x 300mm	5013969985672	82054000	6
T49017 15	SensoPlus Screwdriver TX 15 x 80mm	5013969980110	82054000	6
T49017 1530	SensoPlus Screwdriver TX 15 x 300mm	5013969985689	82054000	6
T49017 20	SensoPlus Screwdriver TX 20 x 90mm	5013969980127	82054000	6
T49017 25	SensoPlus Screwdriver TX 25 x 90mm	5013969980134	82054000	6
T49025 2575	SensoPlus Parallel Tip Screwdriver 2.5 x 75mm	5013969980172	82054000	6
T49025 3075	SensoPlus Parallel Tip Screwdriver 3.0 x 75mm	5013969980189	82054000	6
T49025 3510	SensoPlus Parallel Tip Screwdriver 3.5 x 100mm	5013969980196	82054000	6
T49025 4125	SensoPlus Parallel Tip Screwdriver 4.0 x 125mm	5013969980219	82054000	6
T49025 5515	SensoPlus Parallel Tip Screwdriver 5.5 x 150mm	5013969980226	82054000	6
T49025 5520	SensoPlus Parallel Tip Screwdriver 5.5 x 200mm	5013969980233	82054000	6
T49052	SensoPlus VDE Screwdriver 5 Piece set PH	5013969980424	82054000	3
T49053	SensoPlus VDE Screwdriver 5 Piece set PZD	5013969980431	82054000	3
T49062	SensoPlus VDE Screwdriver 7 Piece set PH	5013969980448	82054000	3
T49063	SensoPlus VDE Screwdriver 7 Piece set PZD	5013969980455	82054000	3
T49077 1	SensoPlus Screwdriver PH 1 x 250mm	5013969981834	82054000	6
T49077 1300	SensoPlus Screwdriver PH 1 x 300mm	5013969985634	82054000	6
T49077 2	SensoPlus Screwdriver PH 2 x 250mm	5013969981841	82054000	6
T49077 2300	SensoPlus Screwdriver PH 2 x 300mm	5013969985641	82054000	6
T49087 1	SensoPlus Screwdriver PZD/SDV 1 x 250mm	5013969981858	82054000	6
T49087 1300	SensoPlus Screwdriver PZD/SDV 1 x 300mm	5013969985610	82054000	6
T49087 2	SensoPlus Screwdriver PZD/SDV 2 x 250mm	5013969981685	82054000	6
T49087 2300	SensoPlus Screwdriver PZD/SDV 2 x 300mm	5013969985627	82054000	6

Technical product information	Blade/Shaft Made from chrome molybdenum vanadium steel, hardened to 57-59 HRC, Chrome plated with black non peel tip finish. Engineers screwdrivers slotted 5,5; 6,5; 8 and 10mm made from chrome vanadium steel, hardened to 53-55 HRC, black non peel finish. Handle The handle core is polypropylene, injection moulded around the blade with a TPE soft grip over-mould. The handles are shatterproof down to -35°C.
Standards compliance	Slotted screwdrivers DIN 5265, DIN 5263, DIN 5264A PZD/SDV Screwdrivers DIN 5262-B-PZ, DIN 5260-PZ, DIN/ISO 8764-1 & 2 PH Screwdrivers DIN 5262-B-PH, DIN 5260-PH, DIN/ISO 8764-1 & 2
User health and safety information	Users and bystanders are advised to wear safety goggles
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	SensoPlus Screwdrivers are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	Germany

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T49010 075	29	29	170	48				
T49010 100	32	32	205	66				
T49010 125	32	32	230	85				
T49010 150	32	32	255	95				
T49010 175	37	37	295	128				
T49010 200	37	37	320	148				
T49012 0	27	27	145	34				
T49012 1	29	29	175	55				
T49012 2	32	32	205	77				
T49012 3	37	37	270	145				
T49013 0	27	27	145	34				
T49013 1	29	29	175	55				
T49013 2	32	32	205	77				
T49013 3	37	37	270	145				
T49017 06	27	27	155	27				
T49017 07	27	27	155	27				
T49017 08	27	27	155	27				
T49017 09	27	27	155	27				
T49017 10	29	29	175	37				
T49017 1030	29	29	395	47				
T49017 15	29	29	175	40				
T49017 1530	29	29	395	57				
T49017 20	29	29	185	44				
T49017 25	29	29	185	48				
T49025 2575	27	27	160	32				
T49025 3075	27	27	160	33				
T49025 3510	27	27	185	39				
T49025 4125	29	29	220	52				
T49025 5515	32	32	255	83				
T49025 5520	32	32	305	92				
T49052					135	35	310	436
T49053					135	35	310	436

T49062					170	40	320	528
T49063					170	40	320	528
T49077 1	29	29	345	81				
T49077 1300	29	29	395	88				
T49077 2	32	32	355	108				
T49077 2300	32	32	405	120				
T49087 1	29	29	345	81				
T49087 1300	29	29	395	88				
T49087 2	32	32	355	108				
T49087 2300	32	32	405	120				

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T49010 075	105	175	40	344		
T49010 100	115	240	45	479		
T49010 125	115	240	45	593		
T49010 150	115	260	45	653		
T49010 175	110	300	65	876		
T49010 200	110	325	65	996		
T49012 0	85	170	40	254		
T49012 1	105	180	40	386		
T49012 2	115	240	45	545		
T49012 3	110	290	65	978		
T49013 0	85	170	40	254		
T49013 1	105	180	40	386		
T49013 2	115	240	45	545		
T49013 3	110	290	65	978		
T49017 06	105	170	40	218		
T49017 07	105	170	40	218		
T49017 08	105	170	40	218		
T49017 09	105	170	40	218		
T49017 10	105	170	40	278		
T49017 1030	115	400	45	379		
T49017 15	105	180	40	296		
T49017 1530	115	400	45	439		

T49017 20	105	190	40	320		
T49017 25	105	190	40	344		
T49025 2575	105	170	40	248		
T49025 3075	105	170	40	254		
T49025 3510	105	190	40	290		
T49025 4125	105	225	40	368		
T49025 5515	115	260	45	581		
T49025 5520	115	320	45	635		
T49052	143	320	135	1476		
T49053	143	320	135	1476		
T49062	180	325	150	1809		
T49063	180	325	150	1809		
T49077 1	95	350	45	558		
T49077 1300	115	400	45	625		
T49077 2	115	360	45	745		
T49077 2300	115	410	45	817		
T49087 1	95	350	45	558		
T49087 1300	115	400	45	625		
T49087 2	115	360	45	745		
T49087 2300	115	410	45	817		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T49010 075							56	Box
T49010 100							83	Box
T49010 125							83	Box
T49010 150							83	Box
T49010 175							108	Box
T49010 200							108	Box
T49012 0							50	Box
T49012 1							56	Box
T49012 2							83	Box
T49012 3							108	Box
T49013 0							50	Box
T49013 1							56	Box

T49013 2							83	Box
T49013 3							108	Box
T49017 06							56	Box
T49017 07							56	Box
T49017 08							56	Box
T49017 09							56	Box
T49017 10							56	Box
T49017 1030							97	Box
T49017 15							56	Box
T49017 1530							97	Box
T49017 20							56	Box
T49017 25							56	Box
T49025 2575							56	Box
T49025 3075							56	Box
T49025 3510							56	Box
T49025 4125							56	Box
T49025 5515							83	Box
T49025 5520							83	Box
T49052			95	Box			168	Box
T49053			95	Box			168	Box
T49062			120	Box			225	Box
T49063			120	Box			225	Box
T49077 1							72	Box
T49077 1300							97	Box
T49077 2							97	Box
T49077 2300							97	Box
T49087 1							72	Box
T49087 1300							97	Box
T49087 2							97	Box
T49087 2300							97	Box