

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, —, —

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC
H

DIST
—

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD




— SEE SHEET 1

NOTES:

- 1 CONNECTOR MEETS THE REQUIREMENTS ACC. DIN 41612 AND DIN 41611,PART 2 AND 5.
- 2 MATERIAL CONTACT: PHOSPHORBRONZE. MATERIAL HOUSING: GLASSFILLED THERM. POLYESTER.
- 3 AT CONTACTAREA 1,25µm GOLD OVER 1,25µm NICKEL. REMAINDER 1,25µm TIN.
- 4 CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE ON OUTSIDE OF MATING AREA OF ROW c.
- 5 DATUM —A— AND —B— AT BASE OF POSTS.
- 6 SUITABLE FOR AUTO-WIRING.

P.C.B. HOLE DIM. ACTION PIN

DRILLED HOLE : 1,15 ± 0,025 mm
FIN. HOLE : 0,94 to 1,09 mm
AFTER REFLOW : 0,91 to 1,09 mm
Cu-thks : 0,025 to 0,075 mm
SnPb-thks : 0,004 to 0,010 mm



P Q S	ROW		
	a	b	c
32	X	X	X
31	X	X	X
30	X	X	X
29	X	X	X
28	X	X	X
27	X	X	X
26	X	X	X
25	X	X	X
24	X	X	X
23	X	X	X
22	X	X	X
21	X	X	X
20	X	X	X
19	X	X	X
18	X	X	X
17	X	X	X
16	X	X	X
15	X	X	X
14	X	X	X
13	X	X	X
12	X	X	X
11	X	X	X
10	X	X	X
9	X	X	X
8	X	X	X
7	X	X	X
6	X	X	X
5	X	X	X
4	X	X	X
3	X	X	X
2	X	X	X
1	X	X	X

AN ASTERISK „X” DENOTES A SIGNAL CONTACT.

SUPERSEDED BY 5148059-4

3

2

6

4-215614-1

FINISH

MATERIAL

PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R.V.LOKVEN 19NOV86

CHK J.GIBBELS

APVD R.SMEETS

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

96 POS FEMALE CONN. ASS'Y
WITH ACTION-PIN.
FOR 2,4-3,2mm P.C.BOARD THK'S

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-215614

SCALE NTS

SHEET 2 OF 2

REV N1