



General ordering data

Order No.	1304860000
Part designation	DKT 4V 2STB
Version	Disconnect and modular disconnect terminal, 4 mm ² , Screw connection, PA 66, beige, TS 32
EAN	4008190030896
Qty.	50 pc(s).

Additional technical data

Colour of insulating material	beige
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	No
Installation advice	TS 32
Insulating material	PA 66
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	2
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 50 °C, + 100 °C
Product family	SAK Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V2
Version	Test-disconnect terminals

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	2.5 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.13 mm ²
Clamping range, max.	4 mm ²
Type of connection	Screw connection
2nd type of connection	screwed
Connection direction	on side
No. of connections	4
Stripping length	9 mm
Clamping screw	M 3

Conductors for clamping (rated connection)

Blade size	0.6 x 3.5 mm
Tightening torque range	0.5...1.0 Nm
Torque level with DMS electric screwdriver	2
Gauge to IEC 60947-1	A3
Solid, min.	0.5 mm ²
Solid, max.	4 mm ²
Stranded, min.	1.5 mm ²
Stranded, max.	4 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	4 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	2.5 mm ²
Twin wire-end ferrule, min.	0.5 mm ²
Twin wire end ferrule, max.	1.5 mm ²
AWG conductor size, min.	AWG 26
AWG conductor size, max.	AWG 12
AWG conductor size, min.	0.13 mm ²
AWG conductor size, max.	3.31 mm ²

Dimensions

Width	6 mm
Height of lowest version	56.5 mm
Length	65 mm
TS 32 offset	33 mm

Disconnect terminals

Cross-disconnect	without
Integral test socket	Yes
Slitting	Pivoting
Tightening torque range	0.5...1.0 Nm
Torque level with DMS electric screwdriver	2

Rating data

Rated cross-section	4 mm ²
Rated voltage	400 V
Rated impulse voltage	6 kV
Rated current	10 A
Standards	IEC 60947-7-1
Current with max. conductor	10 A
Pollution severity	3

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000902
ETIM 3.0	EC000902

Classifications

eClass 4.1	27-14-11-17
eClass 5.0	27-14-11-26
eClass 5.1	27-14-11-26

Similar products

Order No.	Part designation	Version
0687360000	DKT 4/32	Disconnect and modular disconnect terminal, 4 mm ² , Screw connection, PA 66, beige, TS 32
0412160000	SAKR	Disconnect and modular disconnect terminal, 4 mm ² , Screw connection, PA 66, beige, TS 32
0412260000	SAKR 2STB	Disconnect and modular disconnect terminal, 4 mm ² , Screw connection, PA 66, beige, TS 32
0412280000	SAKR 2STB BL	Disconnect and modular disconnect terminal, 4 mm ² , Screw connection, PA 66, blue, TS 32
0412180000	SAKR BL	Disconnect and modular disconnect terminal, 4 mm ² , Screw connection, PA 66, blue, TS 32