

TABLE MAT

32-xxx-xxxx

Double layer table mat with a dissipative top-layer and a conductive bottom layer

Physical properties

Abrasion resistance:	≤ 200 mm ³ (ISO 4649, Method A)
Hardness:	75 Shore A +/-5 (ISO 7619)
Residual indentation:	≤ 0.2 mm (EN 433)
Thickness:	2.0 mm

Electrical properties

Resistant to ground:	≤10 ⁹ Ω
Surface resistance:	≤1.0 x 10 ⁹ Ω
Compliant to:	IEC 61340-5-1



Dimensions, Features and Part Number

Part Number	Shape	Dimensions	Colour
32-190-1102	Complete Roll	1.22m x 10m	Beige
32-190-1103			Grey
32-190-1104			Blue
32-290-0002	Pre-cut mat	61cm x 90cm	Beige
32-290-0003			Grey
32-290-0004			Blue
32-200-2609	Pre-cut mat, 2x10mm male studs and grounding cord 30-560-1510	61cm x 90cm	Beige
32-200-3609			Grey
32-200-4609			Blue
32-200-2612	Pre-cut mat, 2x10mm male studs and grounding cord 30-560-1510	60cm x 120cm	Beige
32-200-3612			Grey
32-200-4612			Blue
32-190-6006	Pre-cut mat and 3x10mm male studs	60cm x 120cm	Beige
32-190-6009			Grey
32-190-6007			Beige

Other

Other cut sizes and mat equipment available on request