


Cat5e 350MHz Bulk Outdoor-Rated Solid-core PVC Cable - Gray

MODEL NUMBER: **N028-01K-GY**



Description

Tripp Lite's Outdoor Rated UV Resistant PVC Unshielded Cat5e cable is ideal for connecting to outdoor mounted wireless antennas. 4-pair, 24 AWG, solid conductors, handle long distance runs with low attenuation loss. Jacket is sequentially marked every two feet for easy measuring. Operating temperature range of -40C to +60C. UL1666 Riser and CMX Outdoor ratings. 1000-ft. Pull box; 26lbs. shipping weight. For pre-terminated patch cables, please browse "N007-" in the search box.

Features

- UV Rated jacket prevents drying and cracking
- 4PR Solid conductors for Low Attenuation Loss
- CMX Outdoor rating; Temp range: -40F to +140F
- 1000-ft. Pull-box, length marked every two feet
- Terminate with Tripp Lite N030-010 Solid wire Cat5e RJ45 plugs

Specifications

OVERVIEW	
Intended Application	Computer Networking
Style	Cat5/5e
Model Type	Bulk Cables
Cable Types	CAT5/CAT5E
INPUT	
Cable Length (ft.)	1000

Highlights

- UV Rated jacket prevents drying and cracking
- 4PR Solid conductors for Low Attenuation Loss
- CMX Outdoor rating; Temp range -40F to +140F

Applications

Excellent for running Cat5e cable to Outdoor Wireless Antennas

Package Includes

1000ft. Box Cat5e Outdoor Rated PVC Bulk Cable

Cable Length (m)	304.80
UPC ASSIGNMENT	
Unit Carton UPC#	037332141491
PHYSICAL	
Shipping Weight (lbs.)	26
Shipping Weight (kg)	11.79
Color	Gray
CONNECTIONS	
Connector A	RJ45 (MALE)
Connector B	RJ45 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.