

SMD MOLDED HIGH CURRENT CHIP INDUCTORS

AIMS-1210H



RoHS
Compliant



3.2 x 2.5 x 2.2mm

FEATURES:

- High Current Capacity
- Heat Resistance Molded Resin
- High Reliability

APPLICATIONS:

- VCRs, Video Cameras
- Automobile Audio Systems
- Computer Products & Peripherals
- LCD TVs, portable VCRs

ELECTRICAL SPECIFICATIONS:

PARAMETERS

ABRACON P/N:	AIMS-1210H-xxx Series
Operating temperature:	-40°C to + 85°C
Storage temperature:	-55°C to + 125°C

Part No.	L(μH)	Tolerance	Q	Test Freq.	SRF(MHz)	DCR(Ω)	Idc(mA)
		(%)	(min)	(MHz)	(min)	(max)	(max)
AIMS-1210H-1R0M	1.0	M	10	7.96	100	0.15	850
AIMS-1210H-1R5M	1.5	M	10	7.96	80	0.18	700
AIMS-1210H-2R2M	2.2	M	10	7.96	68	0.23	600
AIMS-1210H-3R3M	3.3	M	10	7.96	54	0.28	500
AIMS-1210H-4R7M	4.7	M	15	7.96	46	0.34	430
AIMS-1210H-6R8M	6.8	M	15	7.96	38	0.42	360
AIMS-1210H-8R2M	8.2	M	15	7.96	32	0.48	320
AIMS-1210H-100K	10	K	15	2.52	30	0.50	300
AIMS-1210H-150K	15	K	15	2.52	26	0.74	250
AIMS-1210H-220K	22	K	15	2.52	21	1.15	210
AIMS-1210H-330K	33	K	15	2.52	17	1.65	170
AIMS-1210H-470K	47	K	15	2.52	14	2.25	150
AIMS-1210H-680K	68	K	15	2.52	12	3.70	120
AIMS-1210H-101K	100	K	15	0.796	10	5.00	100
AIMS-1210H-151K	150	K	20	0.796	8	8.00	85
AIMS-1210H-221K	220	K	20	0.796	7	11.0	70
AIMS-1210H-331K	330	K	20	0.796	6	16.0	60

OPTIONS & PART IDENTIFICATION:

(Left blank if standard)

AIMS -1210H - □□□□ - □

Inductance

Please refer to the table

Packaging



T

Tape and Reel

Tolerance

See Table Above

Q vs. Frequency Characters



ABRACON IS
ISO 9001 / QS 9000
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale **Revised: 02.08.08**

30332 Esperanza, Rancho Santa Margarita, California 92688

tel 949-546-8000 | fax 949-546-8001 | www.abracon.com


SMD MOLDED HIGH CURRENT CHIP INDUCTORS

AIMS-1210H




3.2 x 2.5 x 2.2mm

OUTLINE DRAWING:




TAPE & REEL: Tape and reel 2,000pcs/reel

Dimensions of Tape



ABRACON P/N	A (mm)	B (mm)	K (mm)	P (mm)	W (mm)	PCS/REEL
AIMS-1210H	2.9 ± 0.1	3.7 ± 0.1	2.5	8.0 ± 0.1	12.0 ± 0.3	2000

Dimensions of Reel



series	ΦA	ΦB	ΦC	W
AIMS-1210H	178 ± 2	60 ± 2	13.5 ± 0.5	12.5 ± 0.5

Dimensions: mm

