

F





E

D

C

B

A



NOTE :

1. MATERIAL :

HOUSING : NYLON GLASS FILLED , BLACK,UL94V-0

TERMINAL : COPPER ALLOY THICKNESS = 0.2 MM

SHIELD CASE : STAINLESS STEEL THICKNESS = 0.3 MM

2. PLATING :

TERMINAL:

CONTACT AREA : GOLD 0.76 MICROMETER MINIMUM.

SOLDER TAIL AREA : MATTE TIN 3.8 MICROMETER MIN.

UNDER PLATING : NICKEL 1.27 MICROMETER MINIMUM.

SHIELD CASE :


2.5-4 MICROMETER SOLDERABLE NICKLE PLATING.

3. TAIL & NAIL COPLANARITY 0.08 mm MAXIMUM.

4. PRODUCT SPEC: PS-47153-001.

5. PACKAGE INFORMATION: PER PK-47153-001.

6. COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV DIRECTIVE 2000/53/EC.



RECOMMENDED P.C.B. PATTERN LAYOUT

REVISE EC NO: DRWN:X/SONG CHKD: APPR:HWANG	2007/11/19 2007/11/20 2007/11/28	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
					mm	INCH	DRAWN BY X/SONG	DATE 2006/05/09	TITLE USB SERIES MINI-B REC. ASS'Y DIP TYPE LEAD FREE		
				4 PLACES	± ---	± ---	CHECKED BY	DATE			
				3 PLACES	± ---	± ---	IWANG	2006/05/09			
				2 PLACES	± 0.25	± ---	APPROVED BY	DATE	MOLEX MOLEX INCORPORATED		
				1 PLACE	± 0.25	± ---	JNCHEN	2006/05/09			
B	REV			ANGULAR ± 3 °		MATERIAL NO. 47153-1002		DOCUMENT NO. SD-47153-002		SHEET NO. 1 OF 1	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					