


- Plug-in unit
- Fixed output voltages
- Thermal fuse in transformer
- Can upon request be modified to comply with the standard for electromedical equipment (EN 60601)
- Exchangeable DC plugs
- Plugg-inn enhet
- Faste utgangsspenninger
- Termosikring i transformator
- Kan på forespørsel modifiseres til å tilfredstille medisinsk standard (EN 60601)
- Utskiftbare DC plugger


**Technical specifications**

Input voltage:  
Output voltage:  
Max output power:  
Insulation class:  
Electrical safety standard:  
EMC standards

- Emission:
- Immunity:

**Output terminals**

Cord with/without plug:  
Dimensions excl. plug (LxWxH):  
Weight:

**Tekniske data**


Inngangsspenning:  
Utgangsspenning:  
Maks. utgangseffekt:  
Isolasjonsklasse:  
Elektrisk sikkerhetsstandard:  
EMC standarder

- Emisjon:
- Immunitet:

**Utgangsterminaler**

Sek. ledning med/uten plugg:  
Mål uten plugg (LxBxH):  
Vekt:

230 VAC +6/-10%, 50/60Hz  
3-42 VAC  
15,0 VA  
II  
EN 60065, EN 60742, EN 60950  
EN 61000-6-3  
EN 61000-6-1  
Accessories /Tilbehør  
100 x 51 x 63 mm  
450 g

**VAC**


| Voltage version (VAC)<br>Spenningsversjoner (VAC) | Nominal load (mA)<br>Merkelast (mA) |
|---------------------------------------------------|-------------------------------------|
| 3                                                 | 4000                                |
| 4,5                                               | 3200                                |
| 6                                                 | 2300                                |
| 7,5                                               | 2000                                |
| 9                                                 | 1600                                |
| 10,5                                              | 1400                                |
| 12                                                | 1100                                |
| 15                                                | 1000                                |
| 18                                                | 800                                 |
| 21                                                | 700                                 |
| 24                                                | 500                                 |
| 28                                                | 490                                 |
| 42                                                | 330                                 |

Max. load (A): See diagram  
Maks. last (A): Se kurve