


SR 16



tightening torque/thread 4.0 Nm/M 5 Inspection Test Pattern Size B 7

Type	Cat.-No.		Qty.p.pck.
SR 16	41050.2	beige	50
SR 16	41050.5	blue	50

Ratings:


	UL	CSA	DIN-VDE	IEC
Rated Voltage	600 V	600 V	611 750 V	947-7-1 800 V
Rated Current	85 A AWG 6	70 A	82 A	76 A

Max Rated Cross Section

Single Wire (solid)	2.5-25 mm ²
Stranded Wire (flexible)	2.5-16 mm ²
Wire Size	AWG 12-4

Dimensions	TS 32	TS 35
LxBxH (mm)	50x12x63	50x12x58
Stripped Length	15 mm	

SR 35



tightening torque/thread 5.0 Nm/M 6 Inspection Test Pattern Size B 8

Type	Cat.-No.		Qty.p.pck.
SR 35	41052.2	beige	20
SR 35	41052.5	blue	20

Ratings:

	UL	CSA	DIN-VDE	IEC
Rated Voltage	600 V	600 V	611 750 V	947-7-1 800 V
Rated Current	115 A AWG 2	100 A	135 A	125 A

Max Rated Cross Section

Single Wire (solid)	2.5-50 mm ²
Stranded Wire (flexible)	2.5-35 mm ²
Wire Size	AWG 12-2

Dimensions	TS 32	TS 35
LxBxH (mm)	58x16x76	58x16x71
Stripped Length	20 mm	

Type:	Cat.-No.	Qty.p.pck.	Terminal accessories	Type:	Cat.-No.	Qty.p.pck.
AP 16	2104.2 beige 2104.5 blue	20	End plate	AP 35	2116.2 beige 2116.5 blue	20
TW 16	2105.2 beige 2105.5 blue	20	Isolation partition	TW 35	2117.2 beige 2117.5 blue	20
TRS 1	2003.2 beige	100	Separator			
ES 32/35 Combi	1424.2 beige		End bracket	ES 32/35 Combi	1424.2 beige	
ES 32/K/ST	2827.0	50		ES 32/K/ST	2827.0	50
ES 35/2/K	2826.2 beige		End bracket	ES 35/K/ST	2828.0	
ES 35/K/ST	2828.0	50		HES 35ST	2761.0	50
STB 14/4	2050.0	50	Test socket	STB 16/4	2127.0	50
PS 4	2051.0	20	Test plug	PS 4	2051.0	20
QL 2	2106.0	50	Switchable link			
VH 19	2009.0	100	Connection sleeve			
BS M 3x25	2010.0	100	Screw			
AD 16	2819.0	20	Warning tag (German) Warning tag (English) Plastic screw for warning tag	AD 35	2820.0	20
Q2	2112.0	20	Cross-connection			
Q3	2113.0	20	Cross-connection			
Q4	2114.0	10	Cross-connection			
Q10	2115.0	10	Cross-connection			