



3D Step-file
available on request



Further specifications and options in section „E-G“ / Weitere Spezifikationen und Optionen in Kapitel „E-G“ / Autres spécifications et options au chapitre „E-G“											
Type / Typ / Type	Body / Körper / Corps		Accessories Zubehör Accessoires	Cap / Farbkappe / Cabochon		Light source Lichtquelle Source lum.		Voltage Spannung Tension			
	Surface Oberfläche Surface	Protection Schutzart Protection						Code	V	mA	
955 Screw terminals Schraubanschlüsse Contact à vis All versions also available as flashing units. Put a "F" for flashing at the end of the part#. Alle Versionen auch blinkend erhältlich. Bitte ergänzen Sie ein „F“ am Ende der Artikel#. Version clignotante possible pour tous les modèles. Ajouter la lettre "F" à la référence.	Black Schwarz Noir Material: ABS Material: ABS Matériel: ABS	IP65	Nut & O-Ring Mutter & O-Ring Ecrou & Joint 	B	Blue Blau Bleu	B0	1 LED 3'000mcd 470nm	Blue Blau Bleue	B	12V AC/DC	20
				G	Green Grün Vert	G0	1 LED 3'000mcd 525nm	Green Grün Verte	D	12V AC/DC	20
				R	Red Rot Rouge	R0	1 LED 800mcd 660nm	Red Rot Rouge	J	48V AC/DC	20
				W	White Weiss Blanc	W0	1 LED 1'000mcd 6500K	White Weiss Blanche			
				Y	Yellow Gelb Jaune	Y0	1 LED 800mcd 592nm	Yellow Gelb Jaune			

Operating Temperature -25° to +60°C / Storage Temperature: -25° to +60°C

RoHS compliant

Specifications are subject to change without notice – Änderungen die dem technischen Fortschritt dienen, sind vorbehalten – Réserve de modifications de toutes les données techniques