

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301030027](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Watertite Wet Location Incandescent Hand Lamp Only, 100W with Screw Release
Grounded Vinyl Guard with Ground Clip

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374
UL E59251

General

Product Family Portable Lighting
Series [130103](#)
NEMA Configuration N/A
NEMA Rating NEMA 4X
Outlet None
Overview [Hand Lamps](#)
Product Name Watertite
Type Hand Lamps
UPC 78678861336

Physical

Cord Length - Primary N/A
Cord Length - Secondary N/A
Depth 120.65mm (4.750")
Duty Wet Location
Guard Included Yes
Guard Type Grounded, Insulated, Screw Release
Height 457.20mm (18.000")
Length N/A
Material - Globe Tempered Glass
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 120V AC

Material Info

Engineering Number 1203IGC



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130103](#) Series