THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST
J	

REVISIONS 変更

P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
	A	再作成 REDRAWN	FJ00-0506-98	08APR98	TM	







MOUTING DIMENSIONS FOR P.C.BOARD
プリント基板取付け穴寸法

(TOLERANCES: ±0.1
PITCH TOLERANCES MUST NOT ACCUMULATE.)
(公差: ±0.1 ピッチ公差は累積されないこと)

P.C.BOARD THICKNESS
基板厚 : 1.6mm



1 RECOMMENDED MOUNTING SCREW: PAN-HEADED, TYPE 2 TAPPING SCREW OF 3DIA X 6LENGTH (JIS B1115, B1122), TIGHTENING TORQUE: 39.2N-cm [4Kg-cm] MAX

1 推奨取付ネジ : JIS B1115, B1122 タッピングねじ, なべ2種, 呼び径3, 長さ6、締付トルク : 39.2N-cm [4Kg-cm] 以下

1123393-6	灰色 (GRAY)	1123435-6
嵌合相手ハウジング型番 MATING HOUSING PART NUMBER	色 (COLOR)	型番 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: 単位・粍 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED
一般公差
10以上 : ±0.2
30以上 >10 : ±0.25
100以上 >30 : ±0.3
ANGLE : ±0.3°

MATERIAL 材料: PBT
FINISH 仕上:

DWN: J. Minato 08APR98
CHK: E. Saiki 08APR98
APVD: K. Kishi 08APR98
PRODUCT SPEC 製品規格: 108-5603
APPLICATION SPEC 取付適用規格:
WEIGHT: 6.3g
CUSTOMER DRAWING

AMP 日本エー・エム・ピー株式会社 Kawasaki, Japan

NAME 名称: 040III MULTILOCK CONNECTOR 24POS CAP HOUSING ASSEMBLY WIRE TO BOARD (H) TYPE
040III マルチロック コネクタ 24極 水平型 キャップハウジング アッセンブリ (対基板用)

SIZE	CAGE CODE	DRAWING NO 書号	RESTRICTED TO
A3	00779	C-1123435	-

SCALE 尺度 2:1 SHEET 1 OF 1 REV A

参考図面

Auto2/new/u.customer/sc-0071/u.sc-1123435