







ワンタッチハンドルキャッチ

ONE-TOUCH LOCK HANDLE CATCHES

使用例は181ページ参照
Refer to P.181 for the use example.キーNo.T0230
Key

商品番号 Product No.	RoHS 2D	CAD 2D	備考 Remarks	(H)	W	ϕd	製品質量(g) Mass	コード Code	単価 Price	量販価格 数量 Quantity	Bulk Price 単価 Price
FA-1810-C-2M	●	2D	鍵付き With lock	25	15.5	6.2	995	60807	¥9,200	5個~	¥8,840
							950	60828	¥8,300	5個~	¥7,970
FA-1810-C-2L	●	2D	鍵付き With lock	35	15.5	6.2	1,010	60373	¥9,500	5個~	¥9,120
							965	60374	¥8,500	5個~	¥8,160
FA-810-C-R	●	2D	封印リング Seal ring	図面参照 See the drawings			4	60811	¥80	80個~	¥77

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。



特徴 Feature

- 錠前を除くすべての部品がステンレス製です。
- 耐食性に優れしかも衝撃に強い製品です。
- ハンドルを上から落し込むだけでワンタッチキャッチします。
- 錠前部は防塵シャッター付リバーシブルキーです。
- 既存のハンドルに簡単に取付けられます。
- 封印リングもオプションで取付けられます。
- Excellent resistant to corrosion and impact.
- Catches handle with one touch by simply lowering the handle.
- The lock device has a dustproof shutter and the key is reversible.
- Sealing can be made. The seal ring can optionally be installed.

仕様 • 材質: ステンレス鋼鋳物 (SUS304)

• 表面仕上: パフ研磨

• 付属品: キー2本

用途 • 特装車・コンテナ等のパイプハンドル用

納期 • 標準品・納期お問合せください

備考 • 無線錠・有線錠・非常脱出装置等、色々なオプションがあります。

⚠ 永くご使用頂くために定期的に摺動部に高性能潤滑剤C-985(1367ページ)を塗布してください。

Specifications • Material: Cast stainless steel (SUS304)


• Finish: Buffing

• Accessories: Two keys

Specific use • Pipe handle for specially equipped and containers.

Remarks • Wireless lock, wire lock and the lock system, and the emergency escape mechanisms are optional.

⚠ To prolong the life of the product, apply a regular coating of high-performance lubricant C-985 (P.1367) to the sliding parts.

適用ハンドル断面寸法(最大)
Applicable handle cross section dimension (max.)

FA-1810-C-2M
推奨製品
Recommended products
FA-1825N-2
FA-1814N
FA-1820-1B
FA-1820-2B

