





Quartz Crystal

SMD-version


model	KX – 6T
frequency	12,0 MHz
mode	fundamental
operating temperature	-40° ~ + 85°C
frequency tolerance at +25°C	± 30 ppm
temperature tolerance -40° ~ + 85°C	± 100 ppm
load capacitance C_L	10 pF
series resonance R_1 max.	200 Ohm
aging (first year)	± 2 ppm
shunt capacitance C_O max.	5,0 pF
drive level max.	50 μ W
RoHS	since production start
contents of reel	1000 pcs.
part no.	12.86538



soldering condition



reel diameter 245 mm



suggested soldering pad