







MATERIAL:
HOUSING MATERIAL: PBT
FLAMABILITY RATING: UL94-V0
COLOR: RED
CONTACT MATERIAL: PHOSPHOR BRONZE
CONTACT TYPE: STAMPED
CONTACT PLATING: MATT TIN OVER NICKEL
QUALITY CLASS: 25 MATING CYCLES
PITCH: 2.54 MM PER ROW

ENVIRONNEMENTAL:
OPERATING TEMPERATURE: -40°C UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL:
CURRENT RATING: 1.5 A PER PIN (PCB PIN)
WORKING VOLTAGE: 100VAC
INSULATION RESISTANCE: >1000MOHM
DIELECTRIC WITHSTANDING VOLT.: 500VAC/MN
CONTACT RESISTANCE: 10mOHM MAX


STANDARD
RoHS CERTIFIED: E323964 / MOD. NUMBER 69035710xx7x

SOLDERING:
WAVE PROCESS ONLY

DIMENSION:
DIM.A= 1.27 x No. of Spaces
DIM.B= DIM.A + 3.3
DIM.C= DIM.A + 2.1

AVAILABLE
xx : 4 TO 26 CIRCUITS

PACKAGING:
x = 2 TUBE

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE	 WÜRTH ELEKTRONIK		
G								.X = $\pm$ 0.2
F								
E	27-MAY-11	PCK&DESCRIPTION	GG					
D	07-APR-10	PINNING	JP	APPROVAL: RJ	UNIT: MM	DESCRIPTION: MM MALE CONNECTOR WITHOUT LATCH AND WITH POLARIZATION		SIZE
C	09-MAR-10	STANDARD	JP		SCALE:			
B	27-NOV-07	MODIFICATIONS	EC		SHEET: 1/1	WERI PART NO: 690 357 10 xx 7 x		
A	03-NOV-06	PDF	JP		DRAW: EAGER			
REV	DATE	FILE	BY					A4