

MTA (Mass Termination Assemblies) Printed Circuit Board Connectors




MTA-100 Post Headers — 0.100" Centers

Discrete wire to board — 2-piece interconnection. Insulation displacement wire termination. **MTA Post Headers:** 0.100" Centers. **Insulation:** Polyester. UL94V-0 rated. Natural color. **Posts:** Tin-plated copper alloy. Meets the material requirements to Table 23.1 of UL 1410 Standards for Television Receiver and Video Products*. UL Recognized File No. E 28476. CSA Certified File No. LR17189. *Wire-to-post connectors only.


0.200" Wide Flat Headers

Straight Post — 0.025" Square



Stock No.	Mfr.'s Type	No. of Pos.	Dimension A — In.	EACH	
				1-499	500-999
512-3850	640452-2	2	0.200	.15	.13
512-3851	640452-3	3	0.300	.12	.11
512-3852	640452-4	4	0.400	.25	.23
512-3853	640452-5	5	0.500	.25	.23
512-3854	640452-6	6	0.600	.34	.31
512-3855	640452-7	7	0.700	.40	.36
512-3856	640452-8	8	0.800	.46	.41
512-3857	640452-9	9	0.900	.51	.46
512-3858	1-640452-0	10	1.000	.46	.41


Right Angle Post — 0.025" Square



512-3860	640453-2	2	0.200	.13	.12
512-3861	640453-3	3	0.300	.20	.18
512-3862	640453-4	4	0.400	.26	.24
512-3863	640453-5	5	0.500	.33	.29
512-3864	640453-6	6	0.600	.23	.20
512-3865	640453-7	7	0.700	.42	.37
512-3866	640453-8	8	0.800	.47	.43
512-3868	1-640453-0	10	1.000	.59	.53

0.092" Wide — Narrow Flat Header

Straight Post — 0.025" Square




512-3870	644456-2	2	0.188	.15	.14
512-3871	644456-3	3	0.288	.19	.17
512-3872	644456-4	4	0.388	.24	.22
512-3873	644456-5	5	0.488	.34	.20
512-3874	644456-6	6	0.588	.37	.25
512-3875	644456-7	7	0.688	.32	.29
512-3876	644456-8	8	0.788	.37	.33
512-3877	644456-9	9	0.888	.55	.30
512-3878	1-644456-0	10	0.988	.61	.33
512-3879	1-644456-1	11	1.088	.67	.37
512-3880	1-644456-2	12	1.188	.54	.45
512-3881	1-644456-4	14	1.388	.61	.47

Straight Post — 0.025" Square with Retentive Legs

Stock No.	Mfr.'s Type	No. of Pos.	Dimension A — In.	EACH	
				1-499	500-999
512-3885	644695-4	4	0.388	.28	.25

Right Angle — 0.025" Square




512-3896	644457-2	2	0.188	.10	.09
512-3897	644457-3	3	0.288	.18	.16
512-3899	644457-5	5	0.488	.23	.20
512-3901	644457-6	6	0.588	.25	.22
512-3903	644457-8	8	0.788	.43	.39
512-3905	644457-9	9	0.888	.43	.38
512-3907	1-644457-0	10	0.988	.48	.43
512-3911	1-644457-2	12	1.188	.57	.51
512-3915	1-644457-4	14	1.388	.83	.75

Right Angle — 0.025" Square with Retentive Legs

512-3923	644694-4	4	0.388	.20	.18
----------	----------	---	-------	-----	-----


Polarized Header with Polarized Notches

Straight Post — 0.025" Square



512-3300	640454-2	2	0.200	.08	.07
512-3301	640454-3	3	0.300	.08	.07
512-3302	640454-4	4	0.400	.10	.09
512-3303	640454-5	5	0.500	.11	.10
512-3304	640454-6	6	0.600	.12	.11
512-3305	640454-7	7	0.700	.14	.13
512-3306	640454-8	8	0.800	.15	.13
512-3325	640454-9	9	0.900	.57	.51
512-3307	1-640454-0	10	1.000	.18	.17
512-3329	1-640454-1	11	1.100	.69	.62
512-3308	1-640454-2	12	1.200	.28	.25
512-3332	1-640454-3	13	1.300	.82	.73
512-3309	1-640454-4	14	1.400	.88	.79
512-3310	2-640454-0	20	2.000	1.57	1.41


Right Angle Post — 0.025" Square



Stock No.	Mfr.'s Type	No. of Pos.	Dimension A — In.	EACH	
				1-499	500-999
512-3311	640455-2	2	0.200	.08	.07
512-3296	640455-3	3	0.300	.07	.07
512-3297	640455-4	4	0.400	.10	.09
512-3312	640455-5	5	0.500	.11	.10
512-3298	640455-6	6	0.600	.13	.11
512-3342	640455-7	7	0.700	.14	.13
512-3313	640455-8	8	0.800	.15	.14
512-3299	1-640455-0	10	1.000	.18	.17
512-3384	1-640455-2	12	1.200	.28	.25
512-3386	1-640455-3	13	1.300	.82	.73
512-3415	1-640455-4	14	1.400	.88	.79


Friction Lock Header with Polarized Notches

Straight Post — 0.025" Square



512-3314	640456-2	2	0.200	.07	.06
512-3315	640456-3	3	0.300	.08	.07
512-3316	640456-4	4	0.400	.10	.09
512-3317	640456-5	5	0.500	.11	.10
512-3318	640456-6	6	0.600	.13	.12
512-3319	640456-7	7	0.700	.14	.13
512-3320	640456-8	8	0.800	.15	.14
512-3321	640456-9	9	0.900	.36	.32
512-3322	1-640456-0	10	1.000	.18	.17
512-3323	1-640456-1	11	1.100	.55	.50
512-3324	1-640456-2	12	1.200	.28	.25
512-3458	1-640456-3	13	1.300	.82	.73
512-3326	1-640456-4	14	1.400	.61	.55
512-3327	1-640456-5	15	1.500	.82	.74
512-3328	1-640456-6	16	1.600	.87	.79
512-3330	2-640456-0	20	2.000	1.26	1.13

Right Angle Post — 0.025" Square



512-3333	640457-2	2	0.200	.07	.06
512-3334	640457-3	3	0.300	.08	.07
512-3335	640457-4	4	0.400	.10	.09
512-3336	640457-5	5	0.500	.12	.10
512-3337	640457-6	6	0.600	.12	.11
512-3338	640457-7	7	0.700	.14	.13
512-3339	640457-8	8	0.800	.15	.13
512-3340	640457-9	9	0.900	.57	.51
512-3341	1-640457-0	10	1.000	.17	.15
512-8642	1-640457-2	12	1.200	.28	.25
512-8765	1-640457-4	14	1.400	.88	.79

Check Pricing And Availability Of All Items On The Internet At www.alliedelec.com

ALLIED ► 397