




**MICRO SWITCH**  
a Honeywell Division  
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING  
1DM423

CATALOG LISTING  
1DM423

ISSUE  
6

REPLACES  
PR-5310

CHECK

CHECK

CHECK

DDM/CAD  
DRAWN  
DHD 5 JAN 93

REVISIONS  
A CO-72328  
DHD  
5 JAN 93

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

**CHARACTERISTICS**

OPERATING FORCE - - - - 15 OZ MAX

**ELECTRICAL DATA**


CONTACT ARRANGEMENT  
S P D T

L181

10A 1/2HP 125, 250 OR 277 VAC



THIRD ANGLE PROJECTION



SCALE 2 TO 1

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED  
TOLERANCES ARE

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ± 5°

WEIGHT

**NOTES**

- 1 - WHITE PLASTIC CASE AND BLACK PLASTIC PLUNGER
- 2 - FLAG STYLE QUICK CONNECT RECEPTACLE REQUIRED FOR NORMALLY OPEN TERMINAL IF SWITCH IS WIRED BEFORE MOUNTING
- 3 - NOMINAL CUTOUT DIMENSION FOR PANELS BETWEEN .045 AND .100 SHOULD BE INTERPOLATED BETWEEN 1.115 AND 1.125
- 4 - PUSH TO OPERATE - MOMENTARY, PULL TO OPERATE - MAINTAINED

ANSI Y14.5M-1982 APPLIES