


RoHS




K86X Series

High Density Vertical PCB Mount and Solder Cup

K86X Series Dimensions

Dimensions in mm



Number of Contacts (Shell Size)	Dimensions (Inch/mm)					
	A	A1	B	C	D	E
15 (E)	.643 16.33	.666 16.92	.984 24.99	1.213 30.81	.090 2.29	.010 0.25
26 (A)	.971 24.66	.994 25.25	1.312 33.32	1.541 39.14	.090 2.29	.020 0.51
44 (B)	1.511 38.38	1.534 38.96	1.852 47.04	2.088 53.04	.090 2.29	.020 0.51
62 (C)	2.159 54.84	2.182 55.42	2.500 63.50	2.729 69.32	.094 2.41	.023 0.58

A = Exterior of Female Shell (S) A1 = Interior of Male Shell (P)

D-SUBMINIATURE CONNECTORS

K86X Series

Documentation & Ordering Information

Kycon Part

Part Number Builder

Series	Shell Type	Pin Length	Contact Option	Contact Type	Board Lock Option	Plating Option
--------	------------	------------	----------------	--------------	-------------------	----------------

Series

K86X - D-Subminiature Vertical Connector

Contact Shell Size Option

E - 15 Contacts

A - 26 Contacts

B - 44 Contacts

C - 62 Contacts

Contact Construction

A - Precision Formed, Solder Cup (Not available with BR/J Option)

D - Precision Formed, Vertical pin (PCB Mount)

Contact Type

P - Pin Contact (Plug)

S - Socket Contact (Receptacle)

Mounting Options

Blank - Through Hole

BR - With (4-40) Tin Plated 6.00mm Long Board Locks


BRJ - With (4-40) Tin Plated 6.00mm Long Board Locks
and (4-40) Hex Jack Screws

K - With (4-40) Bushings


KJ - With (4-40) Bushings and (4-40) Hex Jack Screws

R - With Round Riveted Jack Screws


-BR Option



-K Option



-R Option



Plating Option

Blank - Gold Flash

15 - 15μ" Gold

30 - 30μ" Gold

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[K86X-AD-26P-BRJ15](#) [K86X-ED-15P-BRJ30](#) [K86X-ED-15S-RBR30](#)