

Wiha PicoFinish.

The comfortable precision screwdriver.




Colour-coded drive symbols on the rotating cap for easy recognition of the individual screwdrivers.

The PicoFinish is distinguished by top-quality materials and an ergonomic handle design. The comfortable precision screwdriver with multi-component handle, rapid rotating zone and easy-movement rotating cap is a professional tool for all precision work for confined screw applications. To make things even easier for the user working with tiny screws, we've developed a second, smaller handle. The colour-coded marking of the drive symbol on the rotating cap is also new. This makes it easier to recognise the individual screwdrivers when several are being used at once.



The blades are made of top-quality chrome-vanadium-molybdenum steel to ensure a particularly long tool life. They are subsequently through-hardened in a controlled process and chrome-plated. The precise ChromTop® tip ensures a secure hold in the screw head.



The easy-movement rotating cap protects the palm of the hand.



Wiha PicoFinish.

- Ergonomic handle design with soft zone for comfortable work
- Easy-movement rotating cap for rapid hand action
- Colour-coded marking of the drive symbol for easy identification
- Through-hardened, chromeplated blade made of chromevanadium-molybdenum steel for a long tool life
- Wiha ChromTop® tip guarantees a secure hold in the screw head
- Ideal for all fine, filigree applications in electronics and precision-mechanics applications, as well as for DIY and model-building

For slotted screws.

**260P****PicoFinish slotted screwdriver.****Handle with rotating cap and rapid-turning zone.**

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Order-No.	①	↔	⊖	●	↔	↔	↔
00475	0.8	40	0,16	2,0	134	9	10
00476	1.0	40	0,18	2,0	134	9	10
00477	1.2	40	0,2	2,0	134	9	10
00478	1.5	40	0,25	2,0	134	9	10
00479	1.5	60	0,25	2,0	154	9	10
00480	1.8	40	0,3	2,0	134	9	10
00481	1.8	60	0,3	2,0	154	9	10
00482	2.0	40	0,4	2,0	140	18	10
00484	2.0	60	0,4	2,0	160	18	10
00485	2.0	100	0,4	2,0	200	18	10
00486	2.5	50	0,4	2,5	150	18	10
00487	2.5	75	0,4	2,5	175	18	10
00488	2.5	100	0,4	2,5	200	18	10
00490	3.0	50	0,5	3,0	150	18	10
00492	3.0	100	0,5	3,0	200	18	10
00493	3.0	150	0,5	3,0	250	18	10
00495	3.5	60	0,6	3,5	160	18	10
00497	4.0	60	0,8	4,0	160	18	10
00498	4.0	100	0,8	4,0	200	18	10
00499	4.0	150	0,8	4,0	250	18	10

For Phillips and Pozidriv screws.

**261P****PicoFinish Phillips screwdriver.****Handle with rotating cap and rapid-turning zone.**

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Order-No.	⊕	↔	●	↔	↔	↔
00513	PH000	40	2,0	134	9	10
00512	PH00	40	2,0	134	9	10
00514	PH00	60	2,0	154	9	10
00511	PH0	50	3,0	150	18	10
00515	PH0	75	3,0	175	18	10
00516	PH1	60	4,0	160	18	10
00517	PH1	80	4,0	180	18	10
00518	PH1	150	4,0	250	18	10

**262P****PicoFinish Pozidriv screwdriver.****Handle with rotating cap and rapid-turning zone.**

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Order-No.	⊕	↔	●	↔	↔	↔
04461	PZ0	50	3,0	150	18	10
04462	PZ1	60	4,0	160	18	10