


- Very loud, large horn for indoor and outdoor mounting



TECHNICAL SPECIFICATIONS:

Dimensions (Depth x Width x Height): 152 mm x 148 mm x 356 mm

Housing: ABS, high impact, grey

Connection: Screwable connection max. 2,5 mm² cable entry
rubber squeeze grommet 7 - 10 mm

Duty cycle: 100 %

Fixing: Bracket mounting. Sound outlet facing downwards

ORDER SPECIFICATIONS:

	AC ~	Current consumption	DC =	Current consumption
12 V	-		570 052 54	450 mA
24 V	570 052 65	510 mA	570 052 55	350 mA
42 V	570 052 66	250 mA	-	
115 V	570 052 67	190 mA	570 052 57	150 mA
230 V	570 052 68	90 mA	570 052 58	100 mA

TECHNICAL DIAGRAMS

see page 110

