




Colored Split Loom Tubing

561-SL250PERD, 561-SL250PEYW, 561-SL250PEGR,
 561-SL375PERD, 561-SL375PEYW, 561-SL375PEGR, 561-SL500PERD, 561-SL500PEYW 561-SL500PEGR,
 561-SL625PERD, 561-SL625PEYW, 561-SL625PEGR, 561-SL750PERD, 561-SL750PEYW, 561-SL750PEGR,
 561-SL1000PERD, 561-SL1000PEYW, 561-SL1000PEGR

DIMENSIONS: in.

Date Last Revised: 3-20-2014



MOUSER STOCK NO.	Description	A	B	C	Package Type
561-SL250PERD	1/4" Polyethylene Red	0.266	0.395	0.120	100" Roll
561-SL250PEYW	1/4" Polyethylene Yellow	0.266	0.395	0.120	100" Roll
561-SL250PEGR	1/4" Polyethylene Green	0.266	0.395	0.120	100" Roll
561-SL375PERD	3/8" Polyethylene Red	0.419	0.535	0.128	100" Roll
561-SL375PEYW	3/8" Polyethylene Yellow	0.419	0.535	0.128	100" Roll
561-SL375PEGR	3/8" Polyethylene Green	0.419	0.535	0.128	100" Roll
561-SL500PERD	1/2" Polyethylene Red	0.505	0.670	0.143	100" Roll
561-SL500PEYW	1/2" Polyethylene Yellow	0.505	0.670	0.143	100" Roll
561-SL500PEGR	1/2" Polyethylene Green	0.505	0.670	0.143	100" Roll
561-SL625PERD	5/8" Polyethylene Red	0.650	0.825	0.145	100" Roll
561-SL625PEYW	5/8" Polyethylene Yellow	0.650	0.825	0.145	100" Roll
561-SL625PEGR	5/8" Polyethylene Green	0.650	0.825	0.145	100" Roll
561-SL750PERD	3/4" Polyethylene Red	0.761	0.927	0.144	100" Roll
561-SL750PEYW	3/4" Polyethylene Yellow	0.761	0.927	0.144	100" Roll
561-SL750PEGR	3/4" Polyethylene Green	0.761	0.927	0.144	100" Roll
561-SL1000PERD	1" Polyethylene Red	0.909	1.033	0.172	100" Roll
561-SL1000PEYW	1" Polyethylene Yellow	0.909	1.033	0.172	100" Roll
561-SL1000PEGR	1" Polyethylene Green	0.909	1.033	0.172	100' Roll

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

EPD-200922

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[561-SL625PEYW](#) [561-SL750PEYW](#) [561-SL1000PERD](#) [561-SL375PEYW](#) [561-SL625PERD](#) [561-SL500PERD](#) [561-SL750PEGR](#) [561-SL250PERD](#) [561-SL625NYOR](#) [561-SL625PEGR](#) [561-SL375PERD](#) [561-SL1000NYOR](#) [561-SL750PERD](#) [561-SL375NYOR](#) [561-SL250PEYW](#) [561-SL250PEGR](#) [561-SL750NYOR](#) [561-SL1000PEGR](#) [561-SL500PEGR](#) [561-SL500NYOR](#) [561-SL1000PEYW](#) [561-SL375PEGR](#) [561-SL500PEYW](#) [561-SL250NYOR](#) [561-SL250PERD](#) [561-SL625PEYW](#) [561-SL375PEGR](#) [561-SL1000PERD](#) [561-SL750NYOR](#) [561-SL375PERD](#) [561-SL500PEGR](#) [561-SL750PEYW](#) [561-SL1000PEYW](#) [561-SL500NYOR](#) [561-SL750PEGR](#) [561-SL625NYOR](#) [561-SL250PEGR](#) [561-SL750PERD](#) [561-SL500PERD](#) [561-SL250PEYW](#) [561-SL250NYOR](#) [561-SL1000PEGR](#) [561-SL500PEYW](#) [561-SL375NYOR](#) [561-SL625PEGR](#) [561-SL1000NYOR](#) [561-SL375PEYW](#) [561-SL625PERD](#)