



FEATURES:

- Uses a special low-triboelectric cable which has noise attenuating layers surrounding the center conductor.
- The cable is ideal for low power, low frequency measurements.

MATERIALS:

Body: Brass, Tarnish Resistant Plating, Center Contact: Gold Plated Brass

Dielectric: PTFE

Strain Relief: PVC molded directly to cable and connectors

Cable: 22 AWG, stranding 7 x 30 t.c., PVC insulated, 4.95 (.195) O.D.

Marking: "Pomona 4964-SS"

RATINGS:

Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max.

Operating Temperature: +50°C. (+122°F.) Max.

Nominal Impedance: 50 Ohms

Recommended Frequency Range: DC to 10KHz

ORDERING INFORMATION: Model 4964-SS-*

*- Standard Lengths: 12, 24, 26, 48, 60, 96, 120, 144, 180, 240, 300, 360 – Lengths other than those specified are available on special request.