



FCIconnect.com



Copyright FCI

form: A3

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	TIN LEAD	TIN LEAD	LEAD FREE	LEAD FREE
09	30.81	24.99	18.00	16.21	10.96	D09S82C4GL00	D09S82C6GL00	D09S82C4GL00LF	D09S82C6GL00LF
15	39.14	33.32	26.32	24.54	19.18	D15S82C4GL00	D15S82C6GL00	D15S82C4GL00LF	D15S82C6GL00LF
25	53.03	47.04	40.04	38.25	33.12	D25S82C4GL00	D25S82C6GL00	D25S82C4GL00LF	D25S82C6GL00LF
37	69.32	63.50	56.50	54.71	49.68	D37S82C4GL00	D37S82C6GL00	D37S82C4GL00LF	D37S82C6GL00LF
						Gold flash	0.76 µ gold	Gold flash	0.76 µ gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code —				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D—SUB									
ltr M				ecn no ELX-I-18050		dr MP		date 2014/06/23		title FEMALE CONNECTOR DELTA-D EUROSTYLE RIGHT ANGLED PRESS FIT									
																			
																			
										dwg no C01—8646—0227									
										sheet 1 of 1									
										size A3									
										type Product Customer Drawing									
sheet index				revision sheet		M 1													

PDS: Rev :M

STATUS:Released

Printed: Jul 04, 2014