


Terminal boxes KL

without gland plate, depth: 120



Terminal boxes KL

Material:
Enclosure: Sheet steel 1.25 mm;
1.38 mm for KL 1507.510 to
KL 1513.510
Cover: Sheet steel 1.25 mm

Surface finish:
Case and cover:
Dipcoat-primed,
powder-coated on the outside in
textured RAL 7035

Protection category:
IP 66 to EN 60 529/10.91,
Complies with NEMA 4.

Supply includes:
Enclosure, cover with all-round
foamed-in PU seal and cover
screws, including plastic
bushes.

Approvals,
see page 23.

Detailed drawing,
see page 1081.

Width (B1) in mm	Packs of	150	200	200	300	300	300	400	400	400	400	Page
Height (H1) in mm		150	150	200	150	200	300	150	200	300	400	
Depth (T1) in mm		120	120	120	120	120	120	120	120	120	120	
Model No. KL	1	1500.510	1529.510	1502.510	1501.510	1503.510	1507.510	1589.510	1504.510	1508.510	1511.510	
Weight (kg)		1.6	1.8	2.3	2.6	3.0	4.0	3.2	3.6	4.8	6.2	

Accessories												
Mounting plate	1	1560.700	1575.700	1562.700	1561.700	1563.700	1567.700	1576.700	1564.700	1568.700	1571.700	909
Support rail TS 35/7.5	10	2314.000	2315.000	2315.000	2316.000	2316.000	2316.000	2317.000	2317.000	2317.000	2317.000	927

Width (B1) in mm	Packs of	500	500	600	600	600	800	800	Page
Height (H1) in mm		200	300	200	300	400	200	400	
Depth (T1) in mm		120	120	120	120	120	120	120	
Model No. KL	1	1505.510	1509.510	1506.510	1510.510	1512.510	1527.510	1513.510	
Weight (kg)		4.4	5.8	5.7	6.8	8.4	6.8	11.0	

Accessories									
Mounting plate	1	1565.700	1569.700	1566.700	1570.700	1572.700	1574.700	1573.700	909
Support rail TS 35/15	10	2318.000	2318.000	2319.000	2319.000	2319.000	–	–	927
Cover retainer	3 pairs	1591.000	1591.000	1591.000	1591.000	1591.000	1591.000	1591.000	107
Cover hinge	6	1592.000	1592.000	1592.000	1592.000	1592.000	1592.000	1592.000	894

To order terminal boxes in textured RAL 7032 please add extension .210 to the Model No., and for primed terminal boxes use extension .310.
Delivery times available on request.



**Cable gland and multi-seal
inserts,**
Model No. see page 972 – 973.