


ZETTLER MAGNETICS CO., LTD.

EI48-10VA TRANSFORMER AHI SERIES

FEATURES,

- Conform to IEC EN61558-1 Safety Standards
- UL 5085 Approved Class 2&3:UL File No.E214561
(for 2.5VA and 10VA only)
- Dielectric Strength 4200Vrms
- Optional 115/230V input at 50/60Hz
- Material Meet UL 94V-O Flammability Requirement
- Splited Bobbin Wall Slots Eliminates,all Wire Crossovers
- 3 Standard Sizes for a Variety of Power Application

OUTLINE DIMENSIONS



ELECTRONIC SPECIFICATIONS

Part NO	Input Voltage (V)	Series		Parallel		Rated Power (VA)	Certificate	
		Voltage (Vac)	Current (mA)	Voltage (Vac)	Current (mA)		UL	CE
AHI01010	115V/230V	10	1000	5	2000	10VA	•	
AHI01012	115V/230V	12.6	800	6.3	1600	10VA	•	
AHI01016	115V/230V	16	620	8	1250	10VA	•	
AHI01020	115V/230V	20	500	10	1000	10VA	•	
AHI01024	115V/230V	24	420	12	840	10VA	•	
AHI01028	115V/230V	28	60	14	720	10VA	•	
AHI01036	115V/230V	36	28	18	560	10VA	•	