


Fuseholders

MAXI™ Fuse Splashproof Fuseholder

Ideal for high amperage MAXI™ Fuse applications where a protective cover is required for harsh under-the-hood environments.



Specifications

Terminals: Copper Alloy/Tin Plated with integral stainless steel reinforcing spring

Wire Seal: Silicon Rubber

Body: Heat Stabilized Thermoplastic

Cover: Transparent Thermoplastic with integral silicon seal

Rated: 80A (Dependent on application - contact Littelfuse)

Ambient Temp.: -10°C to +80°C

Maxi Fuse Splashproof Holder for 20-70 Amp

Part Number	Description
1520007Z	Cover with Intergal seal
1520004Z	Body with Mounting Tabs (one tab is slotted)
1520005Z	Body with Mounting Tabs
1520006Z	Body without Mounting Tabs
868-095	Blue Wire Seal for 1.5-4mm ² (14-12AWG) Wire
913-064	Single terminal 1.5-4mm ² (14-12AWG) Wire
913-064-001	Reeled terminals 1.5-4mm ² (14-12AWG) Wire
868-096	Gray Wire Seal for 4-10mm ² (10-8AWG) Wire
913-068	Single terminal 4-6mm ² (10AWG) Wire
913-068-001	Reeled terminals 4-6mm ² (10AWG) Wire
913-087	Single terminal 6-10mm ² (8AWG) Wire
913-087-001	Reeled terminals 6-10mm ² (8AWG) Wire

Maxi Fuse Splashproof Holder for 80 Amp

Part Number	Description
1520007Z	Cover with Intergal seal
1520008Z	Body with Mounting Tabs, 80 Amp
1520009Z	Body without Mounting Tabs, 80 Amp
868-096	Gray Wire Seal for 4-10mm ² (10-8AWG) Wire
913-088	Single terminal 8mm ² (8AWG) Wire
913-088-001	Reeled terminals 8mm ² (8AWG) Wire

*It is recommended that cross linked polyethelene (GLX) insulated wire be used, as described in SAE J1128 (Type, FLY in DIN 76722) or equivalent.